



Quality Products. Service Excellence.

Adjustable Rack Shelf *DNRMA Series*

Load rated to 275 lbs (125 kg)

Features



- 14-Gauge steel construction.
- Movable side brackets allow mounting inside or outside rack at 4 different depths
- Designed mainly for open relay racks - works panel mounted on any rack
- Choice of 16-inch or 20-inch deep.
- Available in either 19-inch rack panel width
- Knockdown design ships unassembled for easy handling and shipping protection.
- 275 lbs (125 kg) **load rating**.
- Finished in rugged textured RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases. BAA/TAA-compliant documentation available upon request.
- RoHS and REACH compliant.
- Manufactured in North America.

Accessories

- Hardware for Rack Mounting Solutions





Part No.	Mounting Width	Overall Depth	Rack Units	Mounting Height
DNRMA1916BK1	19.00	16.00	3U	5.25
DNRMA1920BK1	19.00	20.00	3U	5.25

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[DNRMA1916BK1](#) [DNRMA1920BK1](#) [DNRMA2316BK1](#) [DNRMA2320BK1](#)