



Quality Products. Service Excellence.

4000-7000 BTU/H Outdoor Air Conditioner *DTS Series*

Type 3R, 4, 4X, Side Mounting



Description

- Designed for side mounting on any enclosure surface where high capacity system cooling is required.
- Closed loop cooling ensures clean enclosure air is recirculated without ever mixing with contaminated ambient air.
- Optimum air circulation with maximum clearance distance between warm inlet and cold outlet for reduced hot spot locations.

Standards

- UL, cUL, CE
- Complies with
 - IP56
 - NEMA 3R, 4, 4X


Features

- R134a refrigerant.
- Thermostat control accessible from inside enclosure.
- Expansion valve prevents evaporator freeze up while minimizing heavy inrush currents on large BTU/H units.
- Built in condensate evaporator.
- Continuous air circulation from high capacity fans.
- EMI/RFI suppression meets CE.
- Self-diagnostics on startup.
- Fault indication via LED light.
- Provision for door contact allowing power down when enclosure door is opened.
- Gasket, mounting kit and template for enclosure cutout and drilling are included.
- Condensate drain hose and clamp provided.
- Nema 4/4x exterior 304 stainless steel.


Accessories

- | | |
|-------------------------------|---------------------|
| • Remote Door Switches | • Gasket Kits |
| • Water Condensate Evaporator | • Condensate Bottle |


DTS 3181



Front View



Side View



Drilling Template


DTS 3281



Front View



Side View



Drilling Template

Part No.

DTS3181A115N4SS

DTS3181A230N4SS

DTS3181A460N4SS

DTS3281A115N4SS

DTS3281A230N4SS

DTS3281A460N4SS

Electrical Data	DTS3181A115N4SS	DTS3181A230N4SS	DTS3181A460N4SS	DTS3281A115N4SS	DTS3281A230N4SS	DTS3281A460N4SS
Rated Voltage	115 V 60 Hz	230 V 50/60 Hz	460 V 50/60 Hz	115 V 60 Hz	230 V 50/60 Hz	460 V 50/60 Hz
Range of Operation	103-127 V	198-253 V	360-506 V	103-127 V	198-253 V	360-506 V
Power Consumption	845 W	795 W	1200 W	1680 W	1425 W	1400 W
Running Amps	7.51 A	4.49 A	2.25 A	11.6 A	5.55 A	2.6 A
Starting Current	15 A	10 A	15 A	53 A	21.8 A	16 A
Line Cord	Terminal Block	Terminal Block	Terminal Block	Terminal Block	Terminal Block	Terminal Block

	DTS3181A115N4SS	DTS3281A115N4SS
	DTS3181A230N4SS	DTS3281A230N4SS
Refrigeration Data	DTS3181A460N4SS	DTS3281A460N4SS
Cooling Capacity BTU/h (Watts) +95/+95F +35/+35 C	4100 BTU/h (1200 Watts)	6825 BTU/h (2000 Watts)
Type of Refrigerant	R134a	R134a
Regrigerant Charge	400 g	700 g
Adjustable Control Range	+77..+113°F +25..+45°C Factory setting +95°F/+35°C	+77..+113°F +25..+45°C Factory setting +95°F/+35°C
Max. Ambient Air Temp.	+131°F (+55°C)	+131°F (+55°C)
Min. Ambient Air Temp.	+32°F (+0°C)	+32°F (+0°C)
Air Capacity (unrestricted)	Internal Circulation 177 CFM	Internal Circulation 450 CFM
	External Circulation 100 CFM	External Circulation 450 CFM
Condensation Discharge	Condensate Evaporator	Condensate Evaporator
Filter Mat	150 g/m²	150 g/m²
Db Noise Level	<70 dB(A)	<73 dB(A)
Unit Weight	92 lbs (42 kg)	132 lbs (60 kg)
Exterior Case	Stainless Steel	Stainless Steel
Finish SS	304 Stainless Steel # 4 brush	304 Stainless Steel # 4 Brush
NEMA Rating	Enclosures IP 56/NEMA 3R/4	Enclosures IP 56/NEMA 3R/4

Tags: **DTS, air conditioner, cooler, outdoor, high capacity, 7000 BTU, side mounting, NEMA 4X, Type 4X** *Data subject to change without notice*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[DTS3181A115N4SS](#) [DTS3181A230N4SS](#) [DTS3281A115N4SS](#) [DTS3281A230N4SS](#) [DTS3181A460N4SS](#)
[DTS3281A460N4SS](#)