



Quality Products. Service Excellence.

LED Light Kit *FLK LED Series*

UPDATED

Features

- Available in 9.5", 17.5", 26", 34.5", and 38.5" lengths
- Operating voltage 120V AC5 (50/60Hz). Operating temperature -20C to +50C (-4F to +122F)
- Long lamp life of 50,000 hours
- No remote power supplies as unit comes with its own integral LED drivers
- Hardwired via multiple knockouts in lightweight body (wire not included), finished white, and features manually operated ON/OFF switch
- Variable color temperature switch - 3000K - 4000K - 5000K
- Hinged glass diffuser allows easy access to replaceable LED module
- Certified by ETL to UL and CSA Luminaires standards

Accessories

- Remote Door Switches



Part Number	Description	Number LED Modules	Lumens	Energy Use
FLK5LED	9.5" LED Light Kit	1	310	5W
FLK7LED	17.5" LED Light Kit	2	650	10W
FLK10LED	26.0" LED Light Kit	3	1000	15W
FLK15LED	34.5" LED Light Kit	4	1300	20W

Tags: LED, light kit, 120V, lamp, lighting, diffuser, module, *Data subject to change without notice*

driver

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[FLK7LED](#) [FLK17LED](#) [FLK5LED](#) [FLK10LED](#) [FLK15LED](#)