



Quality Products. Service Excellence.

NEMA Type 12 Server Cabinet *HDME Series*

Load rated to 3,000 lbs (1,360 kg)



The HDME is ideal for housing network access equipment in harsh environments such as a factory floor. The HDME features a sealed cabinet with included gland plates for the installation of filter fans. The UL and CSA tested NEMA ratings provide outstanding protection against dust and air contaminants.

Features

- Front and rear solid doors include an installed gland plate for cooling options. Doors open to 135°. Window door option available.
- Reinforced top panel with provisions for optional **HDMELB** lifting eye bolts.
- Frames can be joined together with an optional joining kit.
- A black, cellular neoprene gasket provides tight and secure seal protection from moisture, dust, and air contaminants.
- Available in 42U and 47U mounting heights.
- Available 24" wide. 31.5" is available as a special order.
- Available in 31.5" and 39.37" overall depths.
- Includes adjustable depth mount rails.

Specifications

- The cabinet frame, doors and side panels are constructed in 14-gauge mild steel.
- Square hole 19" mounting rails are constructed of 12-gauge mild steel, include rack unit indicators, and are Zinc-plated to provide superior surface areas for equipment grounding.
- Load tested to 3,000 lbs (1,360 kg) **static load rating**.
- NEMA Rated for UL 508A Type 12 and CSA Type 12. Complies with NEMA Type 12 and IEC 60529 IP54.
- Lift-tested to 900 lbs (408 kg) of equipment load when used with our **HDMELB** lifting eye bolts.
- Grounding studs are provided on the frame, side panels, and doors. The front and rear studs on the cabinet frame conform to PET.
- Finished in textured RAL9005 black powder coat. Also, available in textured light gray upon request.
 - Complies with the Greenguard guidelines for indoor air quality.
- Meets PCI DSS (Payment Card Industry Data Security Standard) compliance requirements.
- TAA-compliant for GSA Schedule purchases.
 - BAA/TAA-compliant documentation available upon request.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

Included Components

- Welded steel frame with factory-installed nylon levelling feet, ground studs, and mounting points for optional casters.
- Two (2) pairs of adjustable depth EIA-compliant square hole punched mounting rails.
- Two (2) solid removable side panels.
- Two (2) solid doors with





- One (1) installed gland plate
- One (1) die-cast locking swing handle
- Two (2) door keys
- One (1) solid top panel.
- Two (2) bottom panels with gland plates
- Four (4) levelling feet
- Starter pack of **CAGKIT1032-50** screws



We're looking at adding a NEMA 4 and 4X version of the HDME. Click here to provide your input.

Accessories

- Climate Control
- Grid System
- Frame Joining Kit
- 10-32 Mounting Hardware
- Rack Mount Locking Storage Drawer
- Power Distribution Units (PDUs)
- 10 AWG Bonding Wire Kits
- Rack Panels
- Tamper Resistant Screws
- Grid Strap Spacer
- Rack and Cabinet Stem Casters
- Universal Rack Shelf
- Adjustable Depth Rack Shelf
- Vertical Cable Tray
- Copper Bonding Busbar
- Liquid-Tight Cordgrips (Nylon)

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
HDME2068BK	81.14	23.62	31.50	42U	75.04	19.00	25.12
HDME20610BK	81.14	23.62	39.37	42U	75.04	19.00	32.99
HDME2268BK	89.02	23.62	31.50	47U	82.91	19.00	25.12
HDME22610BK	89.02	23.62	39.37	47U	82.91	19.00	32.99

Overall height includes leveling feet.

Compatible Filter Fan Specifications

Filter Fan Part No.	Exhaust Filter Part No.	Cutout Dimensions		Colour	Voltage	Power	Airflow (CFM)	Max. Static Pressure (Airflow = 0)
		Height	Width					
PF65000T12BK	PFA60000BK	12.00	12.00	Black	115V	90W	230	74 Pa
PF65000T12BK230	PFA60000BK	12.00	12.00	Black	230V	150W	230	74 Pa
PF66000T12BK	PFA60000BK	12.00	12.00	Black	115V	160W	295	134 Pa
PF66000T12BK230	PFA60000BK	12.00	12.00	Black	230V	150W	295	134 Pa
PF67000T12BK	PFA60000BK	12.00	12.00	Black	115V	195W	368	187 Pa
PF67000T12BK230	PFA60000LG	12.00	12.00	Black	230V	214W	368	187 Pa

Tags: Edge Computing, Proline, Free Standing Cabinet (NEMA 12)

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[HDME20610BK](#) [HDME2068BK](#) [HDME22610BK](#) [HDME2268BK](#)