



*Quality Products. Service Excellence.*

## Type 4 Mild Steel Freestanding Enclosure *HN4 FS Series*

Continuous Hinge Door with Handle



**Panel  
Sold  
Separately**



### Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls with provision for panel mounting or rack mounting of equipment.
- Provides protection where equipment may be hosed down or otherwise be very wet or in specific applications where corrosion is a critical problem.
- Various inner panels, rack mounting rails and swing-out frames are available to provide flexibility in mounting arrangements.

### Construction

- Formed 12 gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Lifting eyes provide for easy enclosure handling.
- Doors are supported with heavy gauge continuous hinges.
- New 3-pt padlocking door handle.
- Seamless poured-in-place gasket.
- Provision for light kit mounting.
- A grounding stud is provided in the enclosure, and a bonding stud is provided on the door.
- Mounting channels are welded inside the enclosure for mounting optional inner panels or rack equipment rails.

### Standards

- UL 508A Type 3R, 4 and 12
- CSA Type 3R, 4 and 12
- Complies with:
  - NEMA Type 3R, 4, 12 and 13
  - IEC 60529, IP66

### Finish

- The cover and enclosure are finished in recoatable smooth ANSI 61 gray powder coating
- Optional inner panels are available in white powder coating or unpainted galvanized steel



We are looking at adding a rack mounting solution similar to this enclosure.  
Click here to provide your input.

### Accessories

- |                    |                       |
|--------------------|-----------------------|
| • Inner Panels     | • Panel Rails         |
| • Swing Out Frames | • Door Stop Kit       |
| • Drip Shield Kit  | • Floor Stand Kit     |
| • Window Kits      | • Climate Control     |
| • Lighting         | • General Accessories |

**New and improved PDF part drawing files with more detail now available.**

Click part number in table below to access PDF, DXF, and STEP files.

Part No.	Enclosure			Optional
	H	W	D	Inner Panel
HN4FS722518	72.06	25.06	18.06	72WFW
HN4FS723124	72.06	31.06	24.06	72XFW
HN4FS723724	72.06	37.06	24.06	72YFW

<sup>1</sup> Refers to optional full height/full width panels. **Depth panels/half height width panels are also available**

Tags: **HN4FS, freestanding, steel, type 4, NEMA 4, rack, panel mount, mounting channel, outdoor, continuous hinge, handle**

*Data subject to change without notice*

© 2025. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[HN4FS723124](#) [HN4FS723724](#) [HN4FS722518](#)