



Quality Products. Service Excellence.

Type 4X Stainless Steel Two Door Freestanding Enclosure HN4 FSTD SS Series

Continuous Hinge Door with Handle

NEW



**Panel
Sold
Separately**



Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

Construction

- Formed 12 gauge 304 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Heavy duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- Dual Access versions have doors front and back.
- 3-pt padlocking door handle.
- Seamless poured-in place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the inner panel.

Standards

- UL 508A Type 3R, 4X and 12
- CSA Type 3R, 4X and 12
- Complies with:
 - NEMA Type 3R, 4X, 12 and 13
 - IEC 60529, IP66

Finish

- Cover and enclosure are natural stainless steel with a smooth brushed finish.

Accessories

- Inner Panels
- Panel Rails
- Door Stop Kit
- Drip Shield Kit
- Window Kits
- Lighting
- Center Panel Supports
- Swing Out Frames
- Top Hat Cable Modules
- Type 12/4, 4X Handle Kits
- Climate Control
- General Accessories

Single Access

Part No.	Enclosure			Optional Full Panel ¹
	H	W	D	
HN4FS604818SS	60.00	48.00	18.00	60AWFW
HN4FS724818SS	72.00	48.00	18.00	72ZFW

Enclosure				
Part No.	H	W	D	Optional Full Panel ¹
HN4FS726018SS	72.00	60.00	18.00	72ZXFW
HN4FS727218SS	72.00	72.00	18.00	72ZYFW
HN4FS904820SS	90.00	48.00	20.00	90BWFW
HN4FS907220SS	90.00	72.00	20.00	90BYFW
HN4FS724824SS	72.00	48.00	24.00	72ZWFW
HN4FS726024SS	72.00	60.00	24.00	72ZXFW
HN4FS727224SS	72.00	72.00	24.00	72ZYFW
HN4FS907224SS	90.00	72.00	24.00	90BYFW
HN4FS726036SS	72.00	60.00	36.00	72ZXFW
HN4FS907236SS	90.00	72.00	36.00	90BYFW

¹ Refers to optional full height/full width panels. Depth panels/half height width panels are also available

Dual Access

Enclosure				
Part No.	H	W	D	Optional Full Panel ¹
HN4FS724824DASS	72.00	48.00	24.00	72ZWFW
HN4FS726024DASS	72.00	60.00	24.00	72ZXFW
HN4FS727224DASS	72.00	72.00	24.00	72ZYFW
HN4FS907224DASS	90.00	72.00	24.00	90BYFW
HN4FS726036DASS	72.00	60.00	36.00	72ZXFW

¹ Refers to optional full height/full width panels. Depth panels/half height width panels are also available

Tags: **HN4FS, freestanding, stainless, stainless steel, 304, control box, Type 4X, two door, NEMA 4X,** *Data subject to change without notice*
continuous hinge, handle, corrosion

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[HN4FS604818SS](#) [HN4FS724818SS](#) [HN4FS724824DASS](#) [HN4FS724824SS](#) [HN4FS726018SS](#)
[HN4FS726024DASS](#) [HN4FS726024SS](#) [HN4FS726036DASS](#) [HN4FS726036SS](#) [HN4FS727218SS](#)
[HN4FS727224DASS](#) [HN4FS727224SS](#) [HN4FS904820SS](#) [HN4FS907220SS](#) [HN4FS907224DASS](#) [HN4FS907224SS](#)
[HN4FS907236SS](#)