



Quality Products. Service Excellence.

Hole Plugs *HP Series*

NEW SIZES



Features

- Designed to seal unused pushbutton holes, conduit openings and knockout holes against dust, oil and water.
- Standard Pushbutton size is 30.5mm; Mini Pushbutton size is 22.5mm
- Steel Hole Plug**
 - Available in 12 sizes.
 - Finished in 2 color options - ANSI 61 gray or RAL7035 Light Gray
 - Oil resistant gasket.
 - Secured with an 10-24 x 0.55" threaded stud and plated wing nut.
 - Recognized component UR & cUR
 - Type 1, 3, 3R, 4, 12 and 13
- Stainless Steel Hole Plugs**
 - Available in 8 sizes.
 - Finished in brushed natural 304 stainless steel finish.
 - Oil resistant gasket.
 - Secured with an 10-24 x 0.55" threaded stud and plated wing nut.
 - Recognized component UR & cUR
 - Type 1, 3, 3R, 4, 4X, 12 and 13

Steel

ANSI 61 Gray	RAL7035 Lt Gray			
Part No.	Part No.	Description	Max Hole Diameter	Plug Diameter
HP22	HP22LG	22mm Mini Pushbutton	0.88	1.22
HP50	HP50LG	.5" Conduit	0.88	1.38
HP75	HP75LG	.75" Conduit	1.06	1.56
HPB	HPBLG	Std. Pushbutton	1.25	1.75
HP100	HP100LG	1" Conduit	1.38	1.88
HP125	HP125LG	1.25" Conduit	1.69	2.19
HP150	HP150LG	1.5" Conduit	2.00	2.50
HP200	HP200LG	2" Conduit	2.50	3.00
HP250	HP250LG	2.5" Conduit	3.00	3.50
HP300	HP300LG	3" Conduit	3.62	4.12
HP350	HP350LG	3.5" Conduit	4.12	4.62
HP400	HP400LG	4" Conduit	4.62	5.12

Stainless Steel

Part No.	Description	Max Hole Diameter	Plug Diameter
HP22SS	22mm Pushbutton	0.88	1.22
HP50SS	.5" Conduit	0.88	1.38
HP75SS	.75" Conduit	1.06	1.56
HPBSS	Std. Pushbutton	1.25	1.75
HP100SS	1" Conduit	1.38	1.88
HP125SS	1.25" Conduit	1.69	2.19
HP150SS	1.5" Conduit	2.00	2.50

Part No.	Description	Max Hole Diameter	Plug Diameter
HP200SS	2" Conduit	2.50	3.00

Tags: **hole plug, steel, stainless steel, conduit, pushbutton, knockout**

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[HP200](#) [HP250](#) [HP75SS](#) [HP50SS](#) [HP22SS](#) [HP200SS](#) [HP100SS](#) [HPBSS](#) [HP350](#) [HP150SS](#) [HPB](#) [HP400](#)
[HP150](#) [HP100](#) [HP125](#) [HP300](#) [HP125SS](#) [HP75](#) [HP22](#) [HP50](#) [HP100LG](#) [HP125LG](#) [HP150LG](#) [HP200LG](#) [HP22LG](#)
[HP250LG](#) [HP300LG](#) [HP350LG](#) [HP400LG](#) [HP50LG](#) [HP75LG](#) [HPBLG](#)