



*Quality Products. Service Excellence.*

## Compact LED Light Kit *LEDLK Series*

Our compact LED light kit provides efficient lighting solution for most enclosure applications without taking up valuable interior space. Available in magnet or screw mounting and AC or DC power options.



### Features

- Housing constructed in transparent plastic.
- Screw mounting and magnet mounting options - see chart.
- Rocker switch or motion sensor options - see chart.
- Easily connect up to ten (10) light kits together in a daisy chain using LEDXXCORDCON cords. (LEDACNS-ECON cannot be daisy chained).
- Connection: 2-pole plug with snap lock; AC: max. 2.5 A / AC 240 V, white connector; DC: max. 2.5 A / DC 60 V, blue connector. (LEDACNS-ECON wired directly, **Cage clamp** connections).
- Requires hard-wired connection using LEDXXCORDPOW power cord with leads and plug or power brick (not included). (LEDACNS-ECON wired directly, not using accessory power cord).



### Specifications

- Standard LED provide 400 Lm at 120° (1,200 Lm at 360° or equivalent 95W light bulb). HD LED provides 1700 Lm.
- Standard LED lamp length 13.82" (350mm), HD LED Lamp length 23.62" (600mm)
- LED temperature 6,000 to 7,000 K.
- Operating / Storage temperature: -40 to +104 °F (-40 to +40 °C) / -40 to +185 °F (-40 to +85 °C).
- Operating / Storage humidity: max. 90 %RH (non-condensing).
- Service life: 60,000 hrs. at 68 °F (20 °C).
- Max. 5W power consumption (~ 75 W incandescent bulb). HD LED 15W power consumption.
- Protection class / Protection type: II (double insulated) / IP20



Note that the cord on this product is intended to be hard-wired. There are currently no standard plug types for this product.

### Gallery



### Accessories

- Power Cords
- Remote Door Switches

LED Light Kits

Part No.	Voltage	On/Off	Mount	Max Daisy Chain
LEDACSWMAG	90-260V AC	Switch	Magnet	10
LEDACMSMAG	90-260V AC	Sensor	Magnet	10
LEDACSWSCR	90-260V AC	Switch	Screw	10
LEDACMSSCR	90-260V AC	Sensor	Screw	10
LEDACNS-ECON	90-260V AC	NA	Screw	NA
LEDDCSWMAG	20-60V DC	Switch	Magnet	10
LEDDCMSMAG	20-60V DC	Sensor	Magnet	10
LEDDCSWSCR	20-60V DC	Switch	Screw	10
LEDDCMSSCR	20-60V DC	Sensor	Screw	10

HD LED Light

Part No.	Voltage	On/Off	Mount	Max Daisy Chain
HDLED120SCR	90-260V AC	Switch	Screw	8

LED Light Kit Cords

Part No.	Type	Source	Length
LEDACCORDPOW	Power Cord w/leads	AC	78.75
LEDDCCORDPOW	Power Cord w/leads	DC	78.75
LEDACCORDCON	Connector/Daisy Chain Cord	AC	39.38
LEDDCCORDCON	Connector/Daisy Chain Cord	DC	39.38

Light Channel Hardware

Part No.	Description
LCMTG1032	Light channel mounting hardware - 4 x spring nuts/10-32 screws

Tags: led, light kit, rocker switch, sensor, light strip

Data subject to change without notice

© 2024. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[LEDACCORDCON](#) [LEDACCORDPOW](#) [LEDACMSMAG](#) [LEDACMSSCR](#) [LEDACSWMAG](#) [LEDACSWSCR](#)  
[LEDDCCORDCON](#) [LEDDCCORDPOW](#) [LEDDCMSMAG](#) [LEDDCMSSCR](#) [LEDDCSWMAG](#) [LEDDCSWSCR](#)  
[LCMTG1032](#)