



Quality Products. Service Excellence.

Formed Steel Rack Panels *PBFS Series*

Also referred to as a Spacer Blank Panel

Features



- Constructed of 16-gauge steel.
- Fits standard 19in EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



Please be advised that the RAL9005 Semi-Gloss Black will be phased out effective January 3, 2025. The replacement is the RAL9005 Matte Black.

Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel



Part No.	Part No.	Part No.	Part No.	Part No.	Panel Height		Qty of
RAL9005	RAL9005	ANSI61	RAL7035	RAL9003	Rack	Panel	Mounting
Semi-Gloss Black	Matte Black	Dark Gray	Light Gray	Matt White	Units	Height	Points
-	PBFS19000BK	-	-	-	1/2U	0.09	2
PBFS19001BK2	PBFS19001BK	PBFS19001GY2	PBFS19001LG2	PBFS19001WH	1U	1.75	4
PBFS19003BK2	PBFS19003BK	PBFS19003GY2	PBFS19003LG2	PBFS19003WH	2U	3.50	4
PBFS19005BK2	PBFS19005BK	PBFS19005GY2	PBFS19005LG2	PBFS19005WH	3U	5.25	4
PBFS19007BK2	PBFS19007BK	PBFS19007GY2	PBFS19007LG2	PBFS19007WH	4U	7.00	4
PBFS19008BK2	PBFS19008BK	PBFS19008GY2	PBFS19008LG2	PBFS19008WH	5U	8.75	4
PBFS19010BK2	PBFS19010BK	PBFS19010GY2	PBFS19010LG2	PBFS19010WH	6U	10.50	8
PBFS19012BK2	PBFS19012BK	PBFS19012GY2	PBFS19012LG2	PBFS19012WH	7U	12.25	8
PBFS19014BK2	PBFS19014BK	PBFS19014GY2	PBFS19014LG2	PBFS19014WH	8U	14.00	8
PBFS19015BK2	PBFS19015BK	PBFS19015GY2	PBFS19015LG2	PBFS19015WH	9U	15.75	8
PBFS19017BK2	PBFS19017BK	PBFS19017GY2	PBFS19017LG2	PBFS19017WH	10U	17.50	8

Tags: Flanged, Folded

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[PBFS19019BK2](#) [PBFS19021BK2](#) [PBFS19012BK2](#) [PBFS19014BK2](#) [PBFS19024GY2](#) [PBFS19031BK2](#)
[PBFS19026BK2](#) [PBFS19005GY2](#) [PBFS19003BK2](#) [PBFS19021GY2](#) [PBFS19003GY2](#) [PBFS19001GY2](#)
[PBFS19024BK2](#) [PBFS19019GY2](#) [PBFS19012GY2](#) [PBFS19007BK2](#) [PBFS19015BK2](#) [PBFS19010BK2](#)
[PBFS19007GY2](#) [PBFS19028BK2](#) [PBFS19017BK2](#) [PBFS19008GY2](#) [PBFS19001BK2](#) [PBFS19029GY2](#)
[PBFS19026GY2](#) [PBFS19014GY2](#) [PBFS19031GY2](#) [PBFS19015GY2](#) [PBFS19022GY2](#) [PBFS19010GY2](#)
[PBFS19005BK2](#) [PBFS19028GY2](#) [PBFS19008BK2](#) [PBFS19017GY2](#) [PBFS19022BK2](#) [PBFS19015LG2](#)
[PBFS19008LG2](#) [PBFS19010LG2](#) [PBFS19014LG2](#) [PBFS19001LG2](#) [PBFS19007LG2](#) [PBFS19003LG2](#)
[PBFS19005LG2](#) [PBFS19012LG2](#) [PBFS19029BK2](#) [PBFS19000BK](#) [PBFS19000BK2](#) [PBFS19001BK](#) [PBFS19003BK](#)
[PBFS19005BK](#) [PBFS19007BK](#) [PBFS19001WH](#) [PBFS19003WH](#) [PBFS19005WH](#) [PBFS19007WH](#) [PBFS19008WH](#)
[PBFS19010WH](#) [PBFS19012WH](#) [PBFS19014WH](#) [PBFS19015WH](#) [PBFS19017WH](#) [PBFS19019WH](#) [PBFS19021WH](#)
[PBFS19017LG2](#) [PBFS19019LG2](#) [PBFS19010BK](#) [PBFS19008BK](#) [PBFS19012BK](#) [PBFS19014BK](#) [PBFS19015BK](#)
[PBFS19017BK](#)