



Quality Products. Service Excellence.

## Type 4X Polyester Wallmount Enclosure PJW Series

Continuous Hinge Door with Twist Latches and 3 Pt Handle



### Application

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures.
- Provides outstanding insulation and protection where equipment may be hosed down or be very wet.
- Ideal in applications with high temperatures or highly corrosive environments.

### Standards

- UL/cUL 508A Type 1, 2, 3, 4, 4X, 12 and 13
- cUL Type 1, 2, 3, 4, 4X, 12 and 13 per CSA 22.2 No. 94
- Complies with
  - NEMA Type 1, 2, 3, 4, 4X, 12 and 13
  - IEC 60529, IP66

### Construction

- Molded fiberglass polyester enclosure with matching cover is easily punched, cut, or drilled.
- Enhanced UV inhibitors protect against outdoor weathering.
- 3/8 collar studs are provided for optional inner panel mounting, hardware included. Note: Sizes 36x36" and larger have 8 collar studs for added stiffness.
- Stainless steel butterfly type "twist latch" door fasteners with padlock provision.
- Captive oil resistant gasket provides a positive seal.
- Integrated mounting flange.
- Operating temperatures between 130°C and -40°C (266°F to -40°F).
- Impact index of 6.78J (5 ft/lb).
- For corrosion resistance information, please refer to table in the **Technical Information** section.

### Finish

- Fiberglass polyester material has a gray finish.
- Optional inner panels are available in white powder coated finished steel.

### Accessories

- Additional Inner Panels
- Window Kits
- General Accessories
- Pole Mounting Kit
- Climate Control

**New and improved PDF part  
drawing files with more detail  
now available.**

Click part number in table below  
to access PDF, DXF, and STEP files.

Latch	3 Pt Handle	Enclosure			Optional Inner Panel				
		Part No.	Part No.	H	W	D	H	W	Part No.
PJEC363012T	PJEC3630123PT			36.48	30.50	12.18	33.00	27.00	18P3327
PJEC363012TW	PJEC3630123PTW			36.48	30.50	12.18	33.00	27.00	18P3327
PJW363014L	PJW363014L3PT			36.25	30.25	14.13	33.00	27.00	18P3327
PJW363610L	PJW363610L3PT			36.25	36.25	10.13	33.00	33.00	18P3333
PJW363614L	PJW363614L3PT			36.25	36.25	14.13	33.00	33.00	18P3333
PJW483610L	PJW483610L3PT			48.25	36.25	10.13	45.00	33.00	18P4533
PJW483614L	PJW483614L3PT			48.25	36.25	14.13	45.00	33.00	18P4533
PJW603610L	PJW603610L3PT			60.25	36.25	10.13	57.00	33.00	18P5733
PJW603614L	PJW603614L3PT			60.25	36.25	14.13	57.00	33.00	18P5733

Parts ending in W have window. Alternative inner panel options also available.

Tags: **PJ, polyester, fiberglass, non-metallic, window, wallmount, NEMA 4X, Type 4X, outdoor, continuous hinge, twist latch, 3 point handle, nema box**

*Data subject to change without notice*

© 2025. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[PJW363014L](#) [PJW603614L](#) [PJW483610L](#) [PJW363614L](#) [PJW363010L](#) [PJW603610L](#) [PJW483614L](#) [PJW363610L](#)  
[PJEC363012T](#) [PJEC3630123PT](#) [PJEC3630123PTW](#) [PJEC363012TW](#) [PJW483610L3PT](#) [PJW483614L3PT](#)  
[PJW603614L3PT](#) [PJW363610L3PT](#) [PJW363014L3PT](#) [PJW363614L3PT](#) [PJW603610L3PT](#)