



Quality Products. Service Excellence.

Luran Water-Tight Enclosures *R290 Series*

technoPLUS

Key Features:

- Premium UV-resistant Luran plastic enclosures for outdoor applications
- Shallow lid, deep body
- Captive stainless steel lid screws
- Enclosure can be mounted to wall or shelf after closing the lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Silicone gasket included, rated -50°C up to +140°C (-58°F to 284°F)
- Degree of protection: NEMA 4X, IP 66
- Enclosure is light grey (RAL 7035) Luran with UL 94HB flammability rating
- Clip-on design covers made of plastic polypropylene (PP) in anthracite grey (RAL 7016)



Features:



Snap in design covers hide both lid screws and installation holes.



Integrated recesses for membrane keypads.



Enclosure can be installed after closing lid.



Standoffs in the enclosure and lid for panels, PC boards, and components.

Part Number	Length (mm)	Width (mm)	Height (mm)
R290-090-000	130.00	90.00	70.00
R290-112-000	160.00	110.00	70.00
R290-092-000	180.00	90.00	70.00
R290-132-000	230.00	130.00	90.00
R290-172-000	270.00	170.00	90.00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[R290-090-000](#) [R290-092-000](#) [R290-112-000](#) [R290-132-000](#) [R290-172-000](#)