



Quality Products. Service Excellence.

Economy Fixed Depth Wall Rack *RB-WR Series*

Load rated up to 50 lbs (22 kg)

Features

- Available in 1U, 2U, and 4U mounting heights.
- It is hinged for easy rear access to devices.
- Fixed depth of 6 inches.

Specifications

- Constructed in 16-gauge steel.
- Round hole 19" mounting rails are constructed in 16-gauge steel.
- Includes ten **CLPKIT10-32-10** black rack screws with washers and clip nuts.
- Up to 50 lbs (22 kg) **static load rating**.
- Finished in RAL9005 black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
 - BAA/TAA-compliant documentation available upon request.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



RACK BASICS®

A HAMMOND BRAND



Part of the Rack Basics® line of economy rack solutions

Accessories

- Cable Managers
- PDUs and Outlet Strips
- Mounting Screw and Clip Nut Combo-Pack
- Ground Stud Kit



Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Weight Capacity
	Height	Width	Depth		Height	Width	Depth	
RB-WR1	1.88	19.36	6.00	1U	1.75	19.00	5.75	10 lbs (4 kg)
RB-WR2	3.62	19.36	6.00	2U	3.50	19.00	5.75	20 lbs (9 kg)
RB-WR4	7.12	19.36	6.00	4U	7.00	19.00	5.75	50 lbs (22 kg)

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[RB-WR1](#) [RB-WR4](#) [RB-WR2](#)