



*Quality Products. Service Excellence.*

## Adjustable Rack Mount DIN Rail Kit *RMAD Series*

### Features



- Mounts to standard EIA 19" rack rails.
- Includes a 0.3" thick, top-hat standard DIN rail.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Finished in RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

### RMAD (Light Duty) Features



- Constructed of 14 and 16-gauge steel.
- Provides up to 8.38" of adjustable depth for DIN rail-mounted equipment.
- Cutouts on both the rear and sides provide cable pass-through.
- 26 lbs (11 kg) **load rating**.

### RMHD (Heavy Duty) Features

- Constructed of 14-gauge steel.
- Provides up to 8.00" of depth options for DIN rail-mounted equipment.
- 100 lbs (45 kg) **load rating**.

### Accessories

- Hardware for Rack Mounting Solutions
- Hook and Loop Convenience Roll





Part No.	Mounting Dimensions			DIN Rail Overall Dimensions		Weight Capacity
	Height	Rack Units	Depth	Width	Depth	
RMAD19003BK	3.50	2U	11.25	17.18	0.30	26 lbs
RMHD19003BK	3.50	2U	9.25	16.88	0.30	100 lbs

Tags: Industrial Automation Bracket, TransRack

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[RMAD19003BK](#) [RMHD19003BK](#)