



Quality Products. Service Excellence.

Swing Out Wall Mount Cabinet *SWC Series*

Note: This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **HWM Series**. For alternative solution assistance, **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



Features

- Constructed in 14-gauge steel.
- One (1) pair of EIA compliant 10-32 tapped 19" mounting rails.
- Available in two (2) depths and three (3) heights.
- Ventilated center section.
- Lockable, smoked acrylic front door.
- Doors can be reversed hinged (by removing both doors and rotating mid section).
- Lockable, rear wall mount section with keyhole wall mounting.
- Cable access knockouts top and bottom.
- Tested to nearly double the suggested load rating of 200 lbs (91 kg).
- RoHS Compliant.
- Manufactured in North America.

Part No.	Overall Dimensions			Mounting Dimensions			Rack Units
	Height	Width	Depth	Height	Width	Center Depth	
SWC19221BK1	26.00	21.38	17.63	22.75	19.00	11.00	13U
SWC19351BK1	38.25	21.38	17.63	35.00	19.00	11.00	20U
SWC19491BK1	52.25	21.38	17.63	49.00	19.00	11.00	28U
SWC19222BK1	26.00	21.38	26.63	22.75	19.00	20.00	13U
SWC19352BK1	38.25	21.38	26.63	35.00	19.00	20.00	20U
SWC19492BK1	52.25	21.38	26.63	49.00	19.00	20.00	28U

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[SWC193520BK1](#) [SWC192211BK1](#) [SWC194911BK1](#) [SWC192220BK1](#) [SWC194920BK1](#) [SWC193511BK1](#)