



Quality Products. Service Excellence.

Filter Fan Grills *XPFA Series*




Features

- Create your own filter fans or exhaust grills
- Mounts easily with 4 screws using template and hardware provided.
- Designed to meet IP5X dust resistance.
- Includes flame retardant ABS plastic grill and flame retardant synthetic filter.
- Integral EVA foam gasket on the reverse side of grill seals against the mounting surface.
- Hole cutout is NOT critical as the rear of the filter grill seals to the surface (see rear photo below)
- Can be used with standard 3.15" or 4.7" **square fans** or alone as an exhaust grill
- Available in a choice of four colors to match our racks & accessories.
 - "BK" (Black)
 - "CG" (Gray/Beige - RAL7032)
 - "GY" (ANSI 61 Gray)
 - "LG" (Light Gray - RAL7035)



This product does NOT maintain NEMA Type Ratings. Please see our **NEMA Rated Filter Fans**.

Gallery



Part No. Black	Part No. Gray/Beige	Part No. ANSI 61 Gray	Part No. Light Gray	Overall Dimensions			Use With Square Fan Size
				H	W	D	
XPFA80BK	XPFA80CG	XPFA80GY	XPFA80LG	4.14	4.14	0.63	3.15
XPFA120BK	XPFA120CG	XPFA120GY	XPFA120LG	5.91	5.91	0.94	4.70
XPFA150BK	XPFA150CG	XPFA150GY	XPFA150LG	7.72	7.72	0.94	6.00
XPFA254BK	XPFA254CG	XPFA254GY	XPFA254LG	12.00	12.00	0.94	10.00

Replacement Filters (Sold in Pack of 5)

Part No.	Use with Fan Size	Use with XPFA Series	Use with DNFF Series
PFF1000	3.15	XPFA80	DNFF080
PFF2000	4.70	XPFA120	DNFF120
PFF4000	7.72	XPFA150	DNFF150
PFF6000	12.00	XPFA254	DNFF254

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[XPFA120BK](#) [XPFA120GY](#) [XPFA120CG](#) [PFF1000](#) [XPFA80BK](#) [XPFA80GY](#) [XPFA80CG](#) [PFF2000](#) [XPFA80LG](#)
[XPFA120LG](#) [XPFA254CG](#) [XPFA254GY](#) [XPFA254LG](#) [XPFA254BK](#) [PFF6000](#) [XPFA150GY](#) [XPFA150BK](#)
[XPFA150CG](#) [XPFA150LG](#) [PFF4000](#)