





A
board drillings



A
contact arrangement





24 press-in contacts

☒ = press-in contact


□ = position without contact



B (2:1)



2 hole diameter is to be co-ordinated with the respective contact

1 recommended configuration of plated holes
and further information see: DS 09032100001

09 03 224 8840	min. 1,27 µm Au over Ni
part no.	contact surface 

		All Dimensions in mm Original Size DIN A3		Scale 1:1		Free size tol. IEC 60603-2		Ref. complementary IEC 60603-2	
								Sub.	
	All rights reserved			Created by ZWHR		Inspected by DAHMS		Standardisation HOFFMANN	
	Department EC PD - DE							Date 2017-01-20	
HARTING Electronics GmbH D-32339 Espelkamp				Title DIN Signal type M24-flat female press-in 4.5 24-pole					Doc-Key / ECM-Nr. 100072218/UGD/087/B 500000114090
				Type TB	Number 09032248830				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

9032248830