






PCB layout
view component side
thickness 1,6


coding style table	
	style A: for connectors 6-pole
	style B: for connectors from 10 to 14-pole
	style C: for connectors from 16 to 64-pole

further information
see: DS 09181200001

full range of P/N's and
dimensions shown on page 2/2

	All Dimensions in mm Original Size DIN A3	Scale 2:1	Free size tol. IEC 60603-13	Ref. Sub. TB 09185XXX904/904800 / 500000087654 / 2015-04-08	
	All rights reserved Department EC PD - DE	Created by STORCK	Inspected by TADJE	Standardisation KOHLER	Date 2015-12-21
HARTING Electronics GmbH D-32339 Espelkamp		Title SEK 18 male standard conn straight with long lever 2.9			Doc-Key / ECM-Nr. 100154464/UGD/017/A 500000094595
		Type TB	Number 09185XXX904		Rev. A Page 1/2

see table for coding,
feature arrangement and style



A	1	2		3		4		5		6		7		8	
	no. of contacts	performance level						insulator colour	dimensions						
		PL3		PL2		S4			A max.	C	D	E	G		
	part number	part number	part number	part number	part number	part number									
B	06	09 18 506 7904	09 18 506 6904	09 18 506 5904			grey	27,2	22,86	12,45	2,54 x 2 = 5,08	40,3			
	10	09 18 510 7904	09 18 510 6904	09 18 510 5904				32,3	27,94	17,53	2,54 x 4 = 10,16	45,4			
	14	09 18 514 7904	09 18 514 6904	09 18 514 5904				37,4	33,02	22,61	2,54 x 6 = 15,24	50,4			
	16	09 18 516 7904	09 18 516 6904	09 18 516 5904				39,9	35,56	25,15	2,54 x 7 = 17,78	53,0			
	20	09 18 520 7904	09 18 520 6904	09 18 520 5904				45,0	40,64	30,23	2,54 x 9 = 22,86	58,1			
	24	09 18 524 7904	09 18 524 6904	09 18 524 5904				50,1	45,72	35,91	2,54 x 11 = 27,94	63,2			
	26	09 18 526 7904	09 18 526 6904	09 18 526 5904				52,6	48,26	37,85	2,54 x 12 = 30,48	65,7			
	30	09 18 530 7904	09 18 530 6904	09 18 530 5904				58,0	53,34	43,83	2,54 x 14 = 35,56	68,6			
	34	09 18 534 7904	09 18 534 6904	09 18 534 5904				62,8	58,42	48,01	2,54 x 16 = 40,64	75,8			
	40	09 18 540 7904	09 18 540 6904	09 18 540 5904				70,4	66,04	55,63	2,54 x 19 = 48,26	83,5			
	50	09 18 550 7904	09 18 550 6904	09 18 550 5904				83,1	78,74	68,33	2,54 x 24 = 60,96	96,2			
	60	09 18 560 7904	09 18 560 6904	09 18 560 5904				95,8	91,44	81,03	2,54 x 29 = 73,66	108,9			
C	64	09 18 564 7904	09 18 564 6904	09 18 564 5904			100,9	96,52	86,11	2,54 x 31 = 78,74	113,9				
	06	09 18 506 7904 001	09 18 506 6904 001	09 18 506 5904 001			black	27,2	22,86	12,45	2,54 x 2 = 5,08	40,3			
	10	09 18 510 7904 001	09 18 510 6904 001	09 18 510 5904 001				32,3	27,94	17,53	2,54 x 4 = 10,16	45,4			
	14	09 18 514 7904 001	09 18 514 6904 001	09 18 514 5904 001				37,4	33,02	22,61	2,54 x 6 = 15,24	50,4			
	16	09 18 516 7904 001	09 18 516 6904 001	09 18 516 5904 001				39,9	35,56	25,15	2,54 x 7 = 17,78	53,0			
	20	09 18 520 7904 001	09 18 520 6904 001	09 18 520 5904 001				45,0	40,64	30,23	2,54 x 9 = 22,86	58,1			
	24	09 18 524 7904 001	09 18 524 6904 001	09 18 524 5904 001				50,1	45,72	35,91	2,54 x 11 = 27,94	63,2			
	26	09 18 526 7904 001	09 18 526 6904 001	09 18 526 5904 001				52,6	48,26	37,85	2,54 x 12 = 30,48	65,7			
	30	09 18 530 7904 001	09 18 530 6904 001	09 18 530 5904 001				58,0	53,34	43,83	2,54 x 14 = 35,56	68,6			
	34	09 18 534 7904 001	09 18 534 6904 001	09 18 534 5904 001				62,8	58,42	48,01	2,54 x 16 = 40,64	75,8			
	40	09 18 540 7904 001	09 18 540 6904 001	09 18 540 5904 001				70,4	66,04	55,63	2,54 x 19 = 48,26	83,5			
	50	09 18 550 7904 001	09 18 550 6904 001	09 18 550 5904 001				83,1	78,74	68,33	2,54 x 24 = 60,96	96,2			
60	09 18 560 7904 001	09 18 560 6904 001	09 18 560 5904 001			95,8		91,44	81,03	2,54 x 29 = 73,66	108,9				
D	64	09 18 564 7904 001	09 18 564 6904 001	09 18 564 5904 001			100,9	96,52	86,11	2,54 x 31 = 78,74	113,9				
	06	09 18 506 7904 800	09 18 506 6904 800	09 18 506 5904 800			grey without printing	27,2	22,86	12,45	2,54 x 2 = 5,08	40,3			
	10	09 18 510 7904 800	09 18 510 6904 800	09 18 510 5904 800				32,3	27,94	17,53	2,54 x 4 = 10,16	45,4			
	14	09 18 514 7904 800	09 18 514 6904 800	09 18 514 5904 800				37,4	33,02	22,61	2,54 x 6 = 15,24	50,4			
	16	09 18 516 7904 800	09 18 516 6904 800	09 18 516 5904 800				39,9	35,56	25,15	2,54 x 7 = 17,78	53,0			
	20	09 18 520 7904 800	09 18 520 6904 800	09 18 520 5904 800				45,0	40,64	30,23	2,54 x 9 = 22,86	58,1			
	24	09 18 524 7904 800	09 18 524 6904 800	09 18 524 5904 800				50,1	45,72	35,91	2,54 x 11 = 27,94	63,2			
	26	09 18 526 7904 800	09 18 526 6904 800	09 18 526 5904 800				52,6	48,26	37,85	2,54 x 12 = 30,48	65,7			
	30	09 18 530 7904 800	09 18 530 6904 800	09 18 530 5904 800				58,0	53,34	43,83	2,54 x 14 = 35,56	68,6			
	34	09 18 534 7904 800	09 18 534 6904 800	09 18 534 5904 800				62,8	58,42	48,01	2,54 x 16 = 40,64	75,8			
	40	09 18 540 7904 800	09 18 540 6904 800	09 18 540 5904 800				70,4	66,04	55,63	2,54 x 19 = 48,26	83,5			
	50	09 18 550 7904 800	09 18 550 6904 800	09 18 550 5904 800				83,1	78,74	68,33	2,54 x 24 = 60,96	96,2			
60	09 18 560 7904 800	09 18 560 6904 800	09 18 560 5904 800			95,8		91,44	81,03	2,54 x 29 = 73,66	108,9				
E	64	09 18 564 7904 800	09 18 564 6904 800	09 18 564 5904 800			100,9	96,52	86,11	2,54 x 31 = 78,74	113,9				

	All Dimensions in mm Original Size DIN A3	Scale 1:1	Free size tol.	Ref. Sub. TB 09185XXX904/904800 / 500000087654 / 2015-04-08
	All rights reserved Department EC PD - DE	Created by STORCK	Inspected by TADJE	Standardisation KOHLER
HARTING Electronics GmbH D-32339 Espelkamp		Date 2015-12-21		State Final Release
Title SEK 18 male standard conn straight with long lever 2.9				Doc-Key / ECM-Nr. 100154464/UGD/017/A 50000094595
Type TB	Number 09185XXX904		Rev. A	Page 2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[9185166904](#) [9185267904](#) [9185646904](#)