

1	2	3	4	5	6	7	8				
A								A			
B	performance level			solder process	insulator colour	dimensions			F		
	no. of contacts	PL3 part number	PL2 part number			S4 part number	A max.	C		D	E
C	06	09 18 506 7014	09 18 506 6014	09 18 506 5014	wave soldering	grey	27,2	22,86	12,45	2,54 x 2 = 5,08	36,9
	10	09 18 510 7014	09 18 510 6014	09 18 510 5014			32,3	27,94	17,53	2,54 x 4 = 10,16	42,0
	14	09 18 514 7014	09 18 514 6014	09 18 514 5014			37,4	33,02	22,61	2,54 x 6 = 15,24	47,1
	16	09 18 516 7014	09 18 516 6014	09 18 516 5014			39,9	35,56	25,15	2,54 x 7 = 17,78	49,6
	20	09 18 520 7014	09 18 520 6014	09 18 520 5014			45,0	40,64	30,23	2,54 x 9 = 22,86	54,7
	24	09 18 524 7014	09 18 524 6014	09 18 524 5014			50,1	45,72	35,91	2,54 x 11 = 27,94	59,8
	26	09 18 526 7014	09 18 526 6014	09 18 526 5014			52,6	48,26	37,85	2,54 x 12 = 30,48	62,3
	30	09 18 530 7014	09 18 530 6014	09 18 530 5014			58,0	53,34	43,83	2,54 x 14 = 35,56	68,2
	34	09 18 534 7014	09 18 534 6014	09 18 534 5014			62,8	58,42	48,01	2,54 x 16 = 40,64	72,5
	40	09 18 540 7014	09 18 540 6014	09 18 540 5014			70,4	66,04	55,63	2,54 x 19 = 48,26	80,1
	50	09 18 550 7014	09 18 550 6014	09 18 550 5014			83,1	78,74	68,33	2,54 x 24 = 60,96	92,8
	60	09 18 560 7014	09 18 560 6014	09 18 560 5014			95,8	91,44	81,03	2,54 x 29 = 73,66	105,5
	64	09 18 564 7014	09 18 564 6014	09 18 564 5014			100,9	96,52	86,11	2,54 x 31 = 78,74	110,6
D	06	09 19 506 7014	09 19 506 6014	09 19 506 5014	wave & reflow soldering	beige	27,2	22,86	12,45	2,54 x 2 = 5,08	36,9
	10	09 19 510 7014	09 19 510 6014	09 19 510 5014			32,3	27,94	17,53	2,54 x 4 = 10,16	42,0
	14	09 19 514 7014	09 19 514 6014	09 19 514 5014			37,4	33,02	22,61	2,54 x 6 = 15,24	47,1
	16	09 19 516 7014	09 19 516 6014	09 19 516 5014			39,9	35,56	25,15	2,54 x 7 = 17,78	49,6
	20	09 19 520 7014	09 19 520 6014	09 19 520 5014			45,0	40,64	30,23	2,54 x 9 = 22,86	54,7
	24	09 19 524 7014	09 19 524 6014	09 19 524 5014			50,1	45,72	35,91	2,54 x 11 = 27,94	59,8
	26	09 19 526 7014	09 19 526 6014	09 19 526 5014			52,6	48,26	37,85	2,54 x 12 = 30,48	62,3
	30	09 19 530 7014	09 19 530 6014	09 19 530 5014			58,0	53,34	43,83	2,54 x 14 = 35,56	68,2
	34	09 19 534 7014	09 19 534 6014	09 19 534 5014			62,8	58,42	48,01	2,54 x 16 = 40,64	72,5
	40	09 19 540 7014	09 19 540 6014	09 19 540 5014			70,4	66,04	55,63	2,54 x 19 = 48,26	80,1
	50	09 19 550 7014	09 19 550 6014	09 19 550 5014			83,1	78,74	68,33	2,54 x 24 = 60,96	92,8
	60	09 19 560 7014	09 19 560 6014	09 19 560 5014			95,8	91,44	81,03	2,54 x 29 = 73,66	105,5
	64	09 19 564 7014	09 19 564 6014	09 19 564 5014			100,9	96,52	86,11	2,54 x 31 = 78,74	110,6
E								E			
F									F		
	1	2	3	4	5	6	7	8			

		All rights reserved		Created by STORCK		Inspected by TADJE		Standardisation KOHLER		Date 2015-12-21		State Final Release			
HARTING Electronics GmbH D-32339 Espelkamp				Title SEK 18/19 male STD straight kinked with short lever 2.9								Doc-Key / ECM-Nr. 100154464/UGD/043/A 500000094644			
				Type TB		Number 091X5XXX014						Rev. A		Page 2/2	



All rights reserved
Department EC PD - DE

All Dimensions in mm
Original Size DIN A3

Scale
1:1

Free size tol.

Created by
STORCK

Inspected by
TADJE

Standardisation
KOHLER

Date
2015-12-21

State
Final Release

Title
SEK 18/19 male STD straight kinked with short lever 2.9

Type
TB

Number
091X5XXX014

Doc-Key / ECM-Nr.
100154464/UGD/043/A
500000094644

Rev.
A

Page
2/2

Ref.
Sub. TB 091X5XXX014 / 500000087654 / 2015-04-08

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09185065014](#) [09185066014](#) [09185067014](#) [09185105014](#) [09185106014](#) [09185107014](#) [09185145014](#)
[09185146014](#) [09185147014](#) [09185165014](#) [09185166014](#) [09185167014](#) [09185205014](#) [09185206014](#) [09185207014](#)
[09185265014](#) [09185266014](#) [09185267014](#) [09185345014](#) [09185346014](#) [09185347014](#) [09185405014](#)
[09185406014](#) [09185407014](#) [09185505014](#) [09185506014](#) [09185507014](#) [09185605014](#) [09185606014](#) [09185607014](#)
[09185645014](#) [09185646014](#) [09185647014](#) [09195105014](#) [09195106014](#) [09195107014](#) [09195145014](#)
[09195146014](#) [09195147014](#) [09195165014](#) [09195166014](#) [09195167014](#) [09195205014](#) [09195206014](#) [09195207014](#)
[09195265014](#) [09195266014](#) [09195267014](#) [09195345014](#) [09195346014](#) [09195347014](#) [09195405014](#)
[09195406014](#) [09195407014](#) [09195505014](#) [09195506014](#) [09195507014](#) [09195605014](#) [09195606014](#) [09195607014](#)
[09195645014](#) [09195646014](#) [09195647014](#) [09185307014](#) [09195065014](#) [09185306014](#) [09185305014](#)
[09195305014](#) [09195066014](#) [09195067014](#) [09195307014](#) [09195306014](#)