


Connector Location A





Connector Location B




X
male

Y
male

Loading-Plan
acc. to TIA/EIA 568B



-Protection level: IP20
-Temperature range: -20°C ...+70°C

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by		Inspected by		Standardisation		Date	
Department HCS - RO		STOCHECIC		COSTEA		MUNTEANV		2018-01-30	
HARTING Customised Solutions		Title		RJ Industrial Cable Assembly		Doc-Key / ECM-Nr.		100155413/UGD/028/F	
D-32339 Espelkamp		Type		TB		Number		094575115XX	
						Rev.		F	
								Page	
								1/2	

	1	2	3	4	5	6	7	8
A								
B	43	09457511576	RJ45 Ethernet stranded cable, AWG 26/7, 4x2x0.5/1.0, PUR, Cat. 6A, yellow	Ø 6.7	50			
	42	09457511577			40			
	41	09457511575			30			
	40	09457511574			20			
	39	09457511573			15			
	38	09457511572			10			
	37	09457511571			9			
	36	09457511570			8			
	35	09457511569			7			
	34	09457511568			6			
	33	09457511567			5			
	32	09457511566			4			
	31	09457511565			3			
	30	09457511564			2			
	29	09457511563			1.5			
	28	09457511562			1			
	27	09457511561			0.5			
	26	09457511558	RJ45 Ethernet stranded cable, AWG 26/7, 4x2x0.5/1.0, PVC, Cat. 6A, yellow	Ø 6.6	50			
	25	09457511580			45			
	24	09457511557			40			
	23	09457511560			35			
	22	09457511556			30			
	21	09457511559			25			
	20	09457511553			20			
	19	09457511552			15			
	18	09457511551			10			
	17	09457511531			9			
	16	09457511534			8.5			
	15	09457511530			8			
	14	09457511533			7.5			
	13	09457511529			7			
	12	09457511532			6.5			
	11	09457511528			6			
	10	09457511527			5			
	9	09457511526			4			
	8	09457511525			3			
	7	09457511524			2			
	6	09457511523			1.5			
	5	09457511522			1			
	4	09457511554			0.6			
	3	09457511521			0.5			
	2	09457511502	RJ45 Ethernet stranded cable, AWG 26/7, 2x4x0.5/1.0 outdoor, PVC, Cat. 6A, black	Ø 6.6	35			
	1	09457511501			25			
F	Cont. no.	Part no.	Type of cable	Dim. d[mm]	Dim. a[m]			



Department HCS - RO

HARTING Customised Solutions

D-32339 Espelkamp



All Dimensions in mm

All rights reserved

Created by STOCHECIC

Inspected by COSTEA

Standardisation MUNTEANV

Title RJ Industrial Cable Assembly

Type TB

Doc-Key / ECM-Nr. 100155413/UGD/028/F 500000130695

Rev. F

According to production drawing

State Final Release

Free size tol.

Number 094575115XX

2018-01-30

Page 2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09457511523](#) [09457511525](#) [09457511527](#) [09457511551](#) [09457511553](#) [09457511522](#) [09457511524](#)
[09457511529](#) [09457511531](#) [09457511532](#) [09457511533](#) [09457511534](#) [09457511554](#) [09457511561](#) [09457511563](#)
[09457511565](#) [09457511567](#) [09457511569](#) [09457511572](#) [09457511574](#) [09457511573](#) [09457511521](#)
[09457511564](#) [09457511557](#)