



| 1 |           | 2           |                                                                 | 3             |                      | 4                               |                                                                      | 5             |   | 6         |  | 7 |  | 8 |   |
|---|-----------|-------------|-----------------------------------------------------------------|---------------|----------------------|---------------------------------|----------------------------------------------------------------------|---------------|---|-----------|--|---|--|---|---|
| A |           |             |                                                                 |               |                      |                                 |                                                                      |               |   |           |  |   |  |   | A |
|   |           |             |                                                                 |               |                      |                                 |                                                                      |               |   |           |  |   |  |   |   |
| B | 48        | 09473434048 | RJl Ethernet Stranded Cable,<br>4xAWG 22/7, PVC, Cat. 5+, green | 20            | 92                   | 09473434092                     | RJl Ethernet Trailing Cable,<br>4xAWG 22/7, PUR, Cat. 5+, green      | 2.5           | B |           |  |   |  |   |   |
|   | 47        | 09473434047 |                                                                 | 15            | 91                   | 09473434091                     |                                                                      | 2             |   |           |  |   |  |   |   |
|   | 46        | 09473434046 |                                                                 | 10            | 90                   | 09473434090                     |                                                                      | 1.5           |   |           |  |   |  |   |   |
|   | 45        | 09473434045 |                                                                 | 9             | 89                   | 09473434089                     |                                                                      | 1             |   |           |  |   |  |   |   |
|   | 44        | 09473434044 |                                                                 | 8             | 88                   | 09473434088                     |                                                                      | 0.6           |   |           |  |   |  |   |   |
|   | 43        | 09473434043 |                                                                 | 7.5           | 87                   | 09473434087                     |                                                                      | 0.5           |   |           |  |   |  |   |   |
|   | 42        | 09473434042 |                                                                 | 7             | 86                   | 09473434086                     |                                                                      | 0.3           |   |           |  |   |  |   |   |
|   | 41        | 09473434041 |                                                                 | 6             | 85                   | 09473434085                     |                                                                      | 0.2           |   |           |  |   |  |   |   |
|   | 40        | 09473434040 |                                                                 | 5             | 84                   | 09473434084                     |                                                                      | 100           |   |           |  |   |  |   |   |
|   | 39        | 09473434039 |                                                                 | 4             | 83                   | 09473434083                     |                                                                      | 90            |   |           |  |   |  |   |   |
| C | 38        | 09473434038 | RJl Ethernet Standard Cable,<br>4xAWG 22/1, PVC, Cat. 5+, green | 3.5           | 82                   | 09473434082                     | RJl Ethernet Stranded Cable,<br>4xAWG 22/7, PUR FRNC, Cat. 5+, green | 80            | C |           |  |   |  |   |   |
|   | 37        | 09473434037 |                                                                 | 3             | 81                   | 09473434081                     |                                                                      | 70            |   |           |  |   |  |   |   |
|   | 36        | 09473434036 |                                                                 | 2.5           | 80                   | 09473434080                     |                                                                      | 60            |   |           |  |   |  |   |   |
|   | 35        | 09473434035 |                                                                 | 2             | 79                   | 09473434079                     |                                                                      | 50            |   |           |  |   |  |   |   |
|   | 34        | 09473434034 |                                                                 | 1.5           | 78                   | 09473434078                     |                                                                      | 40            |   |           |  |   |  |   |   |
|   | 33        | 09473434033 |                                                                 | 1             | 77                   | 09473434077                     |                                                                      | 30            |   |           |  |   |  |   |   |
|   | 32        | 09473434032 |                                                                 | 0.6           | 76                   | 09473434076                     |                                                                      | 20            |   |           |  |   |  |   |   |
|   | 31        | 09473434031 |                                                                 | 0.5           | 75                   | 09473434075                     |                                                                      | 15            |   |           |  |   |  |   |   |
|   | 30        | 09473434030 |                                                                 | 0.3           | 74                   | 09473434074                     |                                                                      | 10            |   |           |  |   |  |   |   |
|   | 29        | 09473434029 |                                                                 | 0.2           | 73                   | 09473434073                     |                                                                      | 9             |   |           |  |   |  |   |   |
| D | 28        | 09473434028 | RJl Ethernet Standard Cable,<br>4xAWG 22/1, PVC, Cat. 5+, green | 100           | 72                   | 09473434072                     | RJl Ethernet Stranded Cable,<br>4xAWG 22/7, PVC, Cat. 5+, green      | 8             | D |           |  |   |  |   |   |
|   | 27        | 09473434027 |                                                                 | 90            | 71                   | 09473434071                     |                                                                      | 7.5           |   |           |  |   |  |   |   |
|   | 26        | 09473434026 |                                                                 | 80            | 70                   | 09473434070                     |                                                                      | 7             |   |           |  |   |  |   |   |
|   | 25        | 09473434025 |                                                                 | 70            | 69                   | 09473434069                     |                                                                      | 6             |   |           |  |   |  |   |   |
|   | 24        | 09473434024 |                                                                 | 60            | 68                   | 09473434068                     |                                                                      | 5             |   |           |  |   |  |   |   |
|   | 23        | 09473434023 |                                                                 | 50            | 67                   | 09473434067                     |                                                                      | 4             |   |           |  |   |  |   |   |
|   | 22        | 09473434022 |                                                                 | 40            | 66                   | 09473434066                     |                                                                      | 3.5           |   |           |  |   |  |   |   |
|   | 21        | 09473434021 |                                                                 | 30            | 65                   | 09473434065                     |                                                                      | 3             |   |           |  |   |  |   |   |
|   | 20        | 09473434020 |                                                                 | 20            | 64                   | 09473434064                     |                                                                      | 2.5           |   |           |  |   |  |   |   |
|   | 19        | 09473434019 |                                                                 | 15            | 63                   | 09473434063                     |                                                                      | 2             |   |           |  |   |  |   |   |
| E | 18        | 09473434018 | RJl Ethernet Standard Cable,<br>4xAWG 22/1, PVC, Cat. 5+, green | 10            | 62                   | 09473434062                     | RJl Ethernet Stranded Cable,<br>4xAWG 22/7, PVC, Cat. 5+, green      | 1.5           | E |           |  |   |  |   |   |
|   | 17        | 09473434017 |                                                                 | 9             | 61                   | 09473434061                     |                                                                      | 1             |   |           |  |   |  |   |   |
|   | 16        | 09473434016 |                                                                 | 8             | 60                   | 09473434060                     |                                                                      | 0.6           |   |           |  |   |  |   |   |
|   | 15        | 09473434015 |                                                                 | 7.5           | 59                   | 09473434059                     |                                                                      | 0.5           |   |           |  |   |  |   |   |
|   | 14        | 09473434014 |                                                                 | 7             | 58                   | 09473434058                     |                                                                      | 0.3           |   |           |  |   |  |   |   |
|   | 13        | 09473434013 |                                                                 | 6             | 57                   | 09473434057                     |                                                                      | 0.2           |   |           |  |   |  |   |   |
|   | 12        | 09473434012 |                                                                 | 5             | 56                   | 09473434056                     |                                                                      | 100           |   |           |  |   |  |   |   |
|   | 11        | 09473434011 |                                                                 | 4             | 55                   | 09473434055                     |                                                                      | 90            |   |           |  |   |  |   |   |
|   | 10        | 09473434010 |                                                                 | 3.5           | 54                   | 09473434054                     |                                                                      | 80            |   |           |  |   |  |   |   |
|   | 9         | 09473434009 |                                                                 | 3             | 53                   | 09473434053                     |                                                                      | 70            |   |           |  |   |  |   |   |
| F | 8         | 09473434008 | RJl Ethernet Standard Cable,<br>4xAWG 22/1, PVC, Cat. 5+, green | 2.5           | 52                   | 09473434052                     | RJl Ethernet Stranded Cable,<br>4xAWG 22/7, PVC, Cat. 5+, green      | 60            | F |           |  |   |  |   |   |
|   | 7         | 09473434007 |                                                                 | 2             | 51                   | 09473434051                     |                                                                      | 50            |   |           |  |   |  |   |   |
|   | 6         | 09473434006 |                                                                 | 1.5           | 50                   | 09473434050                     |                                                                      | 40            |   |           |  |   |  |   |   |
|   | 5         | 09473434005 |                                                                 | 1             | 49                   | 09473434049                     |                                                                      | 30            |   |           |  |   |  |   |   |
|   | 4         | 09473434004 |                                                                 | 0.6           | Cont. no.            | Part no.                        |                                                                      | Type of cable |   | Dim. a[m] |  |   |  |   |   |
|   | 3         | 09473434003 |                                                                 | 0.5           | All Dimensions in mm |                                 |                                                                      |               |   |           |  |   |  |   |   |
|   | 2         | 09473434002 |                                                                 | 0.3           | Tech. Character.     |                                 |                                                                      |               |   |           |  |   |  |   |   |
|   | 1         | 09473434001 |                                                                 | 0.2           | Free size tol.       |                                 |                                                                      |               |   |           |  |   |  |   |   |
|   | Cont. no. | Part no.    |                                                                 | Type of cable | Dim. a[m]            | According to production drawing |                                                                      |               |   |           |  |   |  |   |   |
|   | 1         |             |                                                                 | 2             |                      | 3                               |                                                                      | 4             |   | 5         |  | 6 |  | 7 |   |

|                                                   |  |                     |  |                                       |  |                                  |  |                                                          |  |                    |  |                        |  |
|---------------------------------------------------|--|---------------------|--|---------------------------------------|--|----------------------------------|--|----------------------------------------------------------|--|--------------------|--|------------------------|--|
| HARTING                                           |  | All rights reserved |  | Created by<br>STOCHECIC<br>Stocheici  |  | Inspected by<br>COSTEA<br>Costea |  | Standardisation<br>MUNTEANV<br>Muntean                   |  | Date<br>2019-07-18 |  | State<br>Final Release |  |
| HARTING Customised Solutions<br>D-32339 Espelkamp |  |                     |  | Title<br>RJ Industrial Cable Assembly |  |                                  |  | Doc-Key / ECM-Nr.<br>100155469/UGD/026/F<br>500000156280 |  |                    |  |                        |  |
|                                                   |  |                     |  | Type<br>TB                            |  | Number<br>09473434XXX            |  |                                                          |  | Rev.<br>F          |  | Page<br>2/3            |  |



All Dimensions in mm

Tech. Character.

Free size tol.

According to production drawing

All rights reserved  
Department HCS - RO

Created by  
STOCHECIC  
Stochechi

Inspected by  
COSTEA  
Costea

Standardisation  
MUNTEANV  
Muntean

Date  
2019-07-18

State  
Final Release

Title  
RJ Industrial Cable Assembly

Doc-Key / ECM-Nr.  
100155469/UGD/026/F  
500000156280

HARTING Customised Solutions  
D-32339 Espelkamp

Type  
TB

Number  
09473434XXX

Rev.  
F

Page  
2/3

|   | 1         | 2           | 3                                                                       | 4         | 5 | 6 | 7 | 8 |
|---|-----------|-------------|-------------------------------------------------------------------------|-----------|---|---|---|---|
| A |           |             |                                                                         |           |   |   |   |   |
|   | 142       | 09473434140 |                                                                         | 100       |   |   |   |   |
|   | 141       | 09473434139 |                                                                         | 90        |   |   |   |   |
|   | 140       | 09473434138 |                                                                         | 80        |   |   |   |   |
|   | 139       | 09473434137 |                                                                         | 70        |   |   |   |   |
|   | 138       | 09473434136 |                                                                         | 60        |   |   |   |   |
|   | 137       | 09473434135 |                                                                         | 50        |   |   |   |   |
|   | 136       | 09473434134 |                                                                         | 40        |   |   |   |   |
|   | 135       | 09473434142 |                                                                         | 35        |   |   |   |   |
| B | 134       | 09473434133 |                                                                         | 30        |   |   |   |   |
|   | 133       | 09473434141 |                                                                         | 25        |   |   |   |   |
|   | 132       | 09473434132 |                                                                         | 20        |   |   |   |   |
|   | 131       | 09473434131 |                                                                         | 15        |   |   |   |   |
|   | 130       | 09473434130 |                                                                         | 10        |   |   |   |   |
|   | 129       | 09473434129 |                                                                         | 9         |   |   |   |   |
|   | 128       | 09473434128 |                                                                         | 8         |   |   |   |   |
|   | 127       | 09473434127 | RJI Ethernet Stranded Cable,<br>4xAWG 22/7, PVC outdoor, Cat. 5+, black | 7.5       |   |   |   |   |
|   | 126       | 09473434126 |                                                                         | 7         |   |   |   |   |
|   | 125       | 09473434125 |                                                                         | 6         |   |   |   |   |
| C | 124       | 09473434124 |                                                                         | 5         |   |   |   |   |
|   | 123       | 09473434123 |                                                                         | 4         |   |   |   |   |
|   | 122       | 09473434122 |                                                                         | 3.5       |   |   |   |   |
|   | 121       | 09473434121 |                                                                         | 3         |   |   |   |   |
|   | 120       | 09473434120 |                                                                         | 2.5       |   |   |   |   |
|   | 119       | 09473434119 |                                                                         | 2         |   |   |   |   |
|   | 118       | 09473434118 |                                                                         | 1.5       |   |   |   |   |
|   | 117       | 09473434117 |                                                                         | 1         |   |   |   |   |
|   | 116       | 09473434116 |                                                                         | 0.6       |   |   |   |   |
|   | 115       | 09473434115 |                                                                         | 0.5       |   |   |   |   |
| D | 114       | 09473434114 |                                                                         | 0.3       |   |   |   |   |
|   | 113       | 09473434113 |                                                                         | 0.2       |   |   |   |   |
|   | 112       | 09473434112 |                                                                         | 100       |   |   |   |   |
|   | 111       | 09473434111 |                                                                         | 90        |   |   |   |   |
|   | 110       | 09473434110 |                                                                         | 80        |   |   |   |   |
|   | 109       | 09473434109 |                                                                         | 70        |   |   |   |   |
|   | 108       | 09473434108 |                                                                         | 60        |   |   |   |   |
|   | 107       | 09473434107 |                                                                         | 50        |   |   |   |   |
|   | 106       | 09473434106 |                                                                         | 40        |   |   |   |   |
|   | 105       | 09473434105 |                                                                         | 30        |   |   |   |   |
| E | 104       | 09473434104 |                                                                         | 20        |   |   |   |   |
|   | 103       | 09473434103 | RJI Ethernet Trailing Cable,<br>4xAWG 22/7, PUR, Cat. 5+, green         | 15        |   |   |   |   |
|   | 102       | 09473434102 |                                                                         | 10        |   |   |   |   |
|   | 101       | 09473434101 |                                                                         | 9         |   |   |   |   |
|   | 100       | 09473434100 |                                                                         | 8         |   |   |   |   |
|   | 99        | 09473434099 |                                                                         | 7.5       |   |   |   |   |
|   | 98        | 09473434098 |                                                                         | 7         |   |   |   |   |
|   | 97        | 09473434097 |                                                                         | 6         |   |   |   |   |
|   | 96        | 09473434096 |                                                                         | 5         |   |   |   |   |
|   | 95        | 09473434095 |                                                                         | 4         |   |   |   |   |
|   | 94        | 09473434094 |                                                                         | 3.5       |   |   |   |   |
| F | 93        | 09473434093 |                                                                         | 3         |   |   |   |   |
|   | Cont. no. | Part no.    | Type of cable                                                           | Dim. a[m] |   |   |   |   |
|   | 1         | 2           | 3                                                                       | 4         | 5 | 6 | 7 | 8 |

|                                                                                       |  |                                    |  |                               |  |                            |  |                                                    |  |
|---------------------------------------------------------------------------------------|--|------------------------------------|--|-------------------------------|--|----------------------------|--|----------------------------------------------------|--|
|  |  | All Dimensions in mm               |  | Tech. Character.              |  | Free size tol.             |  | According to production drawing                    |  |
|  |  | All rights reserved                |  | Created by STOCHECIC Stocheci |  | Inspected by COSTEA Costea |  | Standardisation MUNTEANV Muntean                   |  |
| Department HCS - RO                                                                   |  | Title RJ Industrial Cable Assembly |  | Date 2019-07-18               |  | State Final Release        |  | Doc-Key / ECM-Nr. 100155469/UGD/026/F 500000156280 |  |
| HARTING Customised Solutions D-32339 Espelkamp                                        |  | Type TB                            |  | Number 09473434XXX            |  | Rev. F                     |  | Page 3/3                                           |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09473434205](#) [09473434207](#) [09473434219](#) [09473434220](#) [09473434223](#) [09473434155](#) [09473434203](#)  
[09473434218](#) [09473434222](#) [09473434201](#) [09473434212](#) [09473434027](#) [09473434024](#) [09473434005](#) [09473434010](#)  
[09473434011](#) [09473434017](#) [09473434021](#) [09473434023](#) [09473434074](#) [09473434022](#) [09473434019](#)  
[09473434016](#) [09473434014](#) [09473434013](#) [09473434015](#) [09473434028](#) [09473434008](#) [09473434026](#) [9473434074](#)