






Connector Location A

Connector Location B



6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
Step	a [m]	XXX

NOTE:

- * For lengths < 1.0m:
 - relative positioning of the connectors to each other will be as presented in the drawing, however with an admissible angular deviation around cable axis of ± 30°
- * For lengths ≥ 1.0m:
 - relative positioning of the connectors to each other not obligatory
- * Ethernet transmission possible for lengths up to 45m

Cat. 6A FRNC Ethernet Cable,
AWG27/7, S/FTP, white

09488787584XXX

Type of cable

Part no.

 All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved Department HCS - RO		Created by MUNTEANV	Inspected by COSTEA	Standardisation AVRAM	Date 2017-07-13	State Final Release	
HARTING Customised Solutions D-32427 Minden		Title RJ Industrial Cable Assembly				Doc-Key / ECM-Nr. 100577971/UGD/006/B 500000122254	
Type TB		Number 09488787584XXX				Rev. B	Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09488787584005](#) [09488787584010](#) [09488787584015](#) [09488787584050](#) [09488787584025](#) [09488787584020](#)
[09488787584030](#)