






Connector Location A

Connector Location B



6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
Step	a [m]	XXX

NOTE:
* For lengths < 1.0m:
- relative positioning of the connectors to each other will be as presented in the drawing, however with an admissible angular deviation around cable axis of ± 30°
* For lengths ≥ 1.0m:
- relative positioning of the connectors to each other not obligatory
* Ethernet transmission possible for lengths up to 45m

Cat. 6A FRNC Ethernet Cable, AWG27/7, S/FTP, grey	09488787585XXX
Type of cable	Part no.

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by	Inspected by	Standardisation	Date	State	
	Department HCS - RO	MUNTEANV	COSTEA	AVRAM	2017-07-13	Final Release	
	Title RJ Industrial Cable Assembly					Doc-Key / ECM-Nr. 100577971/UGD/007/B 500000122254	
HARTING Customised Solutions		Type	Number			Rev.	Page
D-32427 Minden		TB	09488787585XXX			B	1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09488787585020](#) [09488787585003](#) [09488787585005](#) [09488787585100](#) [09488787585030](#) [09488787585050](#)
[09488787585010](#) [09488787585015](#) [09488787585025](#) [09488787585075](#)