




Technical drawing of a mechanical part, showing a cross-section with dimensions 5,3 and 8,2.

Performance level	PL2
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

			Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, female, straight 9 Poles, with turned solder bucket, fixing hole	No?/stab/ Scale 1.5:1
		Detail.	8-JUL-02	CV			
		Insp.	12/01/12	JB			
36283	12/01/12	SD	Stand.				
32802	11/07/05	JMDR	 HARTING EURL F-95972 Paris			TB 09641117240	Blatt/ Page 1 / 1
31058	8-JUL-02	CV					
Mod.	Dot.	Name					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09641117240