



Technical drawing of a mechanical part, showing a cross-section with dimensions 5,4 and 8,3.

Performance level	PL2
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100V
Current rating	7.5 A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION dB
5	1 dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB

				Dat.	Name		D-Sub, male, straight, 9 Poles, with turned solder bucket and fixing hole	No? Mstab/ Scale 1.5:1	
			Detail.	8-JUL-02	CV				
			Insp.	12/01/12	JB				
36283	12/01/12	SD	Stand.			All Dim. in mm Orig. Size DIN A 4			
32802	11/07/05	JMDR	HARTING EURL F-95972 Paris					TB 09641217230	Blatt/ Page 1 / 1
31058	8-JUL-02	CV							
Mod.	Dat.	Name					Sub.		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09641217230](#)