




SPECIFICATION

Mating Cycles	500
Filter type	C
Capacitance	470pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	-
10	1dB
50	10dB
100	15dB
500	35dB
1000	32dB



							Dat.	Name		D-Sub, male, angled, 9 Poles, solder pins, tin plated shell with dimples, brackets, clinch nuts and board-locks	Mo?Ms lab/ Scale 1.5:1	
						Detail.	13/10/05	JMDR				
						Insp.						All Dim. in mm
						Stand.						Orig. Size DIN A 4
09641247223	M3		33240	13/10/05	JMDR	HARTING EURL F-95972 Paris					TB 0964124722x	Blatt / Page 1 / 4
09641247222	UNC 4-40		31058	8-JUL-02	CV							
Part number	Nut thread		Mod.	Dat.	Name							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09641247223](#)