

5

4

3

2

1

SPECIFICATION

Mating Cycles	500
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB






PCB Layout, Component side

D


C

B

A



	Dat.	Name
Detail.	8-JUL-02	CV
Insp.		
Stand.		



D-Sub, male, straight,
15 Poles, solder pins,
tin plated shell with
dimples and clinch nuts

Mo?Mstab/
Scale

1.5:1

09642227238	M3	33079	29/08/05	JMDR
09642227237	UNC 4-40	31058	8-JUL-02	CV
Part number	Nut thread	Mod.	Dat.	Name

HARTING EURL
F-95972 Paris



TB 0964222723x

Sub.

Blatt/ Page

3 / 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09642227237