









Mating Cycles	500
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100V
Current Rating	7,5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	1 dB
10	3 dB
50	12 dB
100	20 dB
500	34 dB
1000	30 dB

PCB layout, component side
thickness 1,6



0964 314 7234	4-40 UNC
0964 314 7235	M3
Part number	Screw-lock thread

All rights reserved Department EL PD HARTING Electronics GmbH D-32339 Espelkamp		All Dimensions in mm Original Size DIN A3 Scale 2:1 Free size tol.	Ref. Sub.		Date 2018-08-28 State Final Release	
Created by ZHUANGJ Inspected by LUOK Standardisation HOFFMANN		Title D-Sub female angled 25-pole turned solder pins Type TB Number 0964314723X		Doc-Key / ECM-Nr. 100801512/UGD/000/A 500000139092 Rev. A Page 1/1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09643147235](#)