



SPECIFICATIONS

Filter type	C
Capacitance	1000 pF±20%
Working voltage	100 V
Current rating	6,5 A

Minimum insertion loss

FREQUENCY (MHz)	ATTENUATION (dB)
5	1
10	3
50	12
100	20
500	34
1000	30

Note: Jack-screws are not pre-mounted to allow mounting from any ends

A				Detail.	Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	Male / Female D-Sub filter adapter, 37 poles, 1000 pF	Maßstab/ Scale 1,5:1
				Insp.					
	34901	01/04/08	BB	Stand.					
	34894	12/03/08	PK						
					03/09/07	JS		TB 09 64 400 7230	Blatt/ Page 1 / 1
			Mod.	Dat.	Name	HARTING EURL F-95972 Paris			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09644007230](#)