

5

4

3

2



1

D

C


B

A



Crimping tool :
 hand tool : 09 99 000 0501
 Die : 09 99 000 0533
 With cables AWG 24 and 26, use tool selection 5
 With cables AWG 28, use tool selection 4
 With cables AWG 30, use tool selection 3

09 69 182 2550	Mating area	1,3 μm Au
	Termination area	1,3 μm Au
Part number	Conductor plating	plating

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-sub, female high voltage contact, straight cable, crimp terminations	Maßstab/ Scale 5:1
			Detail.	09/11/10	SC			
			Insp.					
			Stand.					
			HARTING EURL F-95972 Paris				TB 09 69 182 2550	Blatt/ Page 1 / 1
36157	09/11/10	SC					Sub.	
Mod.	Dat.	Name						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09691822550](#)