



| 1 | | 2 | | 3 | | 4 | | |
|--|-------------|---------------------------|-----------------------|---------------------------|--------------------|----------------|------------------------|--------------|
| No. | Part Number | Packaging | Height e | Total length f | Outer thread a | Inner thread b | c | g |
| A | 1 | 09660009972 | 100 pcs in a bag | 6,2 | 9,8 | 4-40 UNC | 4-40 UNC | 4 min. no |
| | 2 | 09660009974 | 100 pcs in a bag | 6,2 | 9,8 | M3 | 4-40 UNC | 4 min. 5,3 |
| | 3 | 09660009973 | 100 pcs in a bag | 6,2 | 9,8 | 4-40 UNC | M3 | 4 min. 0,9 |
| | 4 | 09660009976 | 100 pcs in a bag | 6,2 | 9,8 | M3 | M3 | 4 min. 3,1 |
| B | 5 | 09660009977 | 100 pcs in a bag | 6,2 | 9,8 | M3 | M2,6 | 4 min. no |
| | 6 | 09670009972 | 100 pcs in a bag | 6,2 | 11 | 4-40 UNC | 4-40 UNC | 3,1 min. no |
| | 7 | 09670009974 | 100 pcs in a bag | 6,2 | 11 | M3 | 4-40 UNC | 3,1 min. 5,3 |
| | 8 | 09670019976 | 100 pcs in a bag | 6,2 | 11 | 4-40 UNC | M3 | 3,1 min. 0,9 |
| C | 9 | 09670019974 | 100 pcs in a bag | 6,2 | 11 | M3 | M3 | 3,1 min. 3,1 |
| | 10 | 09670019956 | 100 pcs in a bag | 5 | 11 | 4-40 UNC | 4-40 UNC | 3,1 min. no |
| | 11 | 09670019956580 | 5000 pcs in a bag | 5 | 11 | 4-40 UNC | 4-40 UNC | 3,1 min. no |
| | 12 | 09670019958 | 100 pcs in a bag | 5 | 11 | M3 | 4-40 UNC | 3,1 min. 4,1 |
| D | 13 | 09670029048 | 100 pcs in a bag | 5 | 11 | 4-40 UNC | M3 | 3,1 min. 0,9 |
| | 14 | 09670019959 | 100 pcs in a bag | 5 | 11 | M3 | M3 | 3,1 min. 2,5 |
| | 15 | 09670019941 | 100 pcs in a bag | 5 | 13 | 4-40 UNC | 4-40 UNC | 3,1 min. no |
| | 16 | 09670019941580 | 5000 pcs in a bag | 5 | 13 | 4-40 UNC | 4-40 UNC | 3,1 min. no |
| E | 17 | 09670019954 | 100 pcs in a bag | 5 | 13 | M3 | 4-40 UNC | 3,1 min. 4,1 |
| | 18 | 09670019954580 | 5000 pcs in a bag | 5 | 13 | M3 | 4-40 UNC | 3,1 min. 4,1 |
| | 19 | 09670019998 | 100 pcs in a bag | 5 | 13 | 4-40 UNC | M3 | 3,1 min. 0,9 |
| | 20 | 09670019947 | 100 pcs in a bag | 5 | 13 | M3 | M3 | 3,1 min. 2,5 |
| F | 21 | 09670019960 | 100 pcs in a bag | 5 | 18 | 4-40 UNC | 4-40 UNC | 3,1 min. no |
| | 22 | 09670019933 | 100 pcs in a bag | 5 | 18 | M3 | 4-40 UNC | 3,1 min. 4,1 |
| | 23 | 09670019932 | 100 pcs in a bag | 5 | 18 | 4-40 UNC | M3 | 3,1 min. 0,9 |
| | 24 | 09670019931 | 100 pcs in a bag | 5 | 18 | M3 | M3 | 3,1 min. 2,5 |
| G | 25 | | | | | | | |
| | 26 | | | | | | | |
| | 27 | | | | | | | |
| | 28 | | | | | | | |
| H | 29 | | | | | | | |
| | 30 | | | | | | | |
| | 31 | | | | | | | |
| | 32 | | | | | | | |
|  All Dimensions in mm Original Size DIN A4 | | Scale 5:1 | Free size tol. | | | Ref. | | |
|  All rights reserved Department EL PD | | Created by ZENGD | Inspected by LUOK | Standardisation KOHLER | Date 2018-08-02 | Sub. | | |
| HARTING Electronics GmbH D-32339 Espelkamp | | Title D-Sub screw lock | | | | | State Final Release | |
| | | Type TB | Number 096X00X9XXX | | | | Rev. A | Page 2/2 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

9670009974