




order contacts separately

Cable description	Cable diameter	Wire gauge	P/N contact	P/N Crimping insert	P/N Crimping Tool	P/N Mounting tool
BETATRANS GW C-FLEX R 600/1000V 4x0.75 sqmm Leoni: 223388	6,0mm	AWG 22-18	09 67 000 3476	0999 000 0649	0999 000 0647	0999 000 0639

		All Dimensions in mm Original Size DIN A4		Scale 1:1		Free size tol.		Ref.					
								Sub.					
		All rights reserved		Created by STOICA		Inspected by AVRAM		Standardisation HOFFMANN		Date 2017-11-03		State Final Release	
		Department EC PD - RO											
HARTING Electronics GmbH D-32339 Espelkamp		Title M12 5-poles A-coded crimpflange female										Doc-Key / ECM-Nr. 100699015/UGD/000/C 500000127343	
		Type TB		Number 21038212512								Rev. C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21038212512](#)