





Connector Location A

Connector Location B



Loading-Plan:

1	wire 1	1
2	wire 2	2
3	wire 3	3
4	wire 4	4
FE	wire 5	FE



- Protection level: IP65/67
 - Temperature range: -40°C ... +80°C

6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
0.5	XXX=005	
0.4	XXX=004	
0.3	XXX=003	
0.2	XXX=002	
Step	a[m]	XXX

OZ-500, PVC grey, 5x2,5mm ²	2133A7A8524XXX
Type of cable	Part no.

All rights reserved Department HCS - RO HARTING Customised Solutions D-32427 Minden	Tech. Character. Free size tol. According to production drawing 2017-02-03	Created by MUNTEANV	Inspected by POPESCU	Standardisation AVRAM	Date 2017-02-09	State Final Release	Doc-Key / ECM-Nr. 100689080/UGD/001/B 500000115250
	Title M12 L-coded Cable Assembly	Type TB	Number 2133A7A8524XXX	Rev. B	Page 1/1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[2133A7A8524010](#) [2133A7A8524020](#) [2133A7A8524050](#) [2133A7A8524150](#) [2133A7A8524200](#) [2133A7A8524100](#)