





Connector Location A

Connector Location B



Loading-Plan:

- 1 brown 1
2 white 2
3 blue 3
4 black 4



4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

- Protection level: IP67
- Temperature range: -25°C ... +80°C

PVC grey, 4x0.25mm²	21348081481XXX
Type of cable	Part no.

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by COSTEA Costea		Inspected by MUNTEANV Muntean		Standardisation MUNTEANV Muntean	
Department HCS - RO		Date 2018-12-18		State Final Release		Doc-Key / ECM-Nr. 100578268/UGD/009/B 500000145065	
HARTING Customised Solutions		Title M8 Cable Assembly 4-poles st/st f/m		Rev. B		Page 1/1	
D-32339 Espelkamp		Type TB		Number 21348081481XXX			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21348081481005](#) [21348081481020](#) [21348081481075](#) [21348081481015](#) [21348081481100](#) [21348081481050](#)
[21348081481010](#) [21348081481040](#) [21348081481060](#) [21348081481030](#)