



Connector Location A

Connector Location B




X
female



Loading-Plan

- 1 brown
- 2 white
- 3 blue
- 4 black

- Protection level: IP67
- Temperature range: -25°C ... +80°C



4.0 to 4.0	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

PUR black, 4x0.25mm²	21348100489XXX
Type of cable	Part no.

		All rights reserved		Created by STOCHECIC Stocheci		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean		Date 2019-01-11		State Final Release	
HARTING Customised Solutions		Department HCS - RO		Title M8 Cable Assembly 4-poles st/- f/-								Doc-Key / ECM-Nr. 100809670/UGD/009/A 500000145294	
D-32339 Espelkamp				Type TB		Number 21348100489XXX						Rev. A	
												Page 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348100489015](#) [21348100489020](#) [21348100489050](#) [21348100489005](#) [21348100489075](#) [21348100489100](#)
[21348100489010](#) [21348100489060](#) [21348100489040](#)