


Connector Location A


Connector Location B




X
male

Loading-Plan


Y
female



- 1 brown
- 2 white
- 3 blue
- 4 black



- Protection level: IP 65/67
- Temperature range: -25°C ... +80°C



4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
Step	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

PUR black, 4x0.34mm ²	21348487491XXX
Type of cable	Part no.

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by STOCHECIC Stocheci		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean	
Department HCS - RO		Date 2018-12-14		State Final Release		Doc-Key / ECM-Nr. 100806544/UGD/009/A 500000144869	
HARTING Customised Solutions		Title M12 Cable Assembly A-cod st/an m/f		Rev. A		Page 1/1	
D-32339 Espelkamp		Type TB		Number 21348487491XXX			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348487491050](#) [21348487491100](#) [21348487491015](#) [21348487491005](#) [21348487491010](#) [21348487491020](#)
[21348487491075](#) [21348487491003](#) [21348487491006](#)