




Connector Location A

Connector Location B



- Loading-Plan:
- 1 brown
  - 3 blue
  - 4 black



|            |           |
|------------|-----------|
| 4.0 to 40  | ±1%       |
| 0.1 to 3.9 | +0.04     |
| a [m]      | Tolerance |

|                       |       |         |
|-----------------------|-------|---------|
| length in "1m" step   | 40    | XXX=40  |
|                       | 39    | XXX=39  |
|                       | .     | .       |
|                       | 12    | XXX=120 |
|                       | 11    | XXX=110 |
| length in "0.1m" step | 10    | XXX=100 |
|                       | 9.9   | XXX=099 |
|                       | 9.8   | XXX=098 |
|                       | .     | .       |
|                       | 0.4   | XXX=004 |
|                       | 0.3   | XXX=003 |
|                       | 0.2   | XXX=002 |
| Step                  | 0.1   | XXX=001 |
|                       | a [m] | XXX     |

|                      |                |
|----------------------|----------------|
| PUR black, 3x0.34mm² | 21348400390XXX |
| Type of cable        | Part no.       |

- Protection level: IP67
- Temperature range: -25°C ... +80°C

|                                                |                     |                                         |                               |                                  |                 |                                                    |          |
|------------------------------------------------|---------------------|-----------------------------------------|-------------------------------|----------------------------------|-----------------|----------------------------------------------------|----------|
| All Dimensions in mm                           |                     | Tech. Character.                        |                               | Free size tol.                   |                 | According to production drawing                    |          |
|                                                | All rights reserved | Created by COSTEA Costea                | Inspected by MUNTEANV Muntean | Standardisation MUNTEANV Muntean | Date 2019-01-14 | State Final Release                                |          |
|                                                | Department HCS - RO | Title M12 Cable Assembly A-cod st/- f/- |                               |                                  |                 | Doc-Key / ECM-Nr. 100806420/UGD/009/A 500000145014 |          |
| HARTING Customised Solutions D-32339 Espelkamp |                     | Type TB                                 | Number 21348500390XXX         |                                  |                 | Rev. A                                             | Page 1/1 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348500390010](#) [21348500390075](#) [21348500390100](#) [21348500390015](#) [21348500390005](#) [21348500390050](#)  
[21348500390020](#)