







Loading-Plan:



- | | | |
|----|-----------|----|
| 1 | brown | 1 |
| 2 | blue | 2 |
| 3 | white | 3 |
| 4 | green | 4 |
| 5 | pink | 5 |
| 6 | yellow | 6 |
| 7 | black | 7 |
| 8 | grey | 8 |
| 9 | red | 9 |
| 10 | violet | 10 |
| 11 | grey-pink | 11 |
| 12 | red-blue | 12 |



4.0 to 100	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

Part no. 21348687CXXXXXX

Type of cable XX
PUR black, 12x0.14mm² XX=78

- Protection level: IP67
- Temperature range: -30°C ... +80°C

	All rights reserved	Scale 2:1	Free size tol.		Ref.
	Department EC PD - RO	Created by TAMAS	Inspected by STOICA	Standardisation HOFFMANN	Sub.
HARTING Electronics GmbH		Title M12 A-coded Cable Assembly			Doc-Key / ECM-Nr. 100591328/UGD/009/A 500000079105
D-32339 Espelkamp		Type TB	Number 21348687CXXXXXX		Rev. A Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348687C78050](#) [21348687C78100](#) [21348687C78005](#) [21348687C78015](#) [21348687C78010](#) [21348687C78020](#)
[21348687C78075](#)