




Connector Location A

Connector Location B



- Protection level: IP67
- Temperature range: -25°C ... +80°C

4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=40
	39	XXX=39
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

PVC grey, 3x0.34mm ²	21348700383XXX
Type of cable	Part no.

All rights reserved
Department HCS - RO
HARTING Customised Solutions
D-32339 Espelkamp

All Dimensions in mm

Tech. Character.

Created by COSTEA Costea

Inspected by MUNTEANV Muntean

Standardisation MUNTEANV Muntean

Date 2019-01-11

State Final Release

Free size tol.

According to production drawing

Title M12 Cable Assembly A-cod an/- f/-

Type TB

Number 21348700383XXX

Doc-Key / ECM-Nr. 100578809/UGD/009/C 500000145017

Rev. C

Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21348700383100](#) [21348700383020](#) [21348700383005](#) [21348700383015](#) [21348700383075](#) [21348700383050](#)
[21348700383010](#)