




Connector Location A

Connector Location B



Loading-Plan:

- 1 brown
- 2 white
- 3 blue
- 4 black



- Protection level: IP 65/67
- Temperature range: -25°C ... +80°C

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

4.0 to 40	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

Part no.	213487004XXXXX
----------	----------------

Type of cable	XX
PVC grey, 4x0.34mm ²	XX=84
PUR black, 4x0.34mm ²	XX=91



All Dimensions in mm

Tech. Character.

Free size tol.

According to production drawing 2016-09-05

All rights reserved

Department HCS - RO

HARTING Customised Solutions

D-32427 Minden

Created by

MUNTEANV

Inspected by

POPESCU

Standardisation

AVRAM

Date

2016-10-18

State

Final Release

Title

M12 A-coded Cable Assembly

Type

TB

Number

213487004XXXXX

Doc-Key / ECM-Nr.

100578836/UGD/009/C

500000110313

Rev.

C

Page

1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348700484050](#) [21348700491010](#) [21348700484010](#)