


Connector Location A




Connector Location B




X
male

Loading-Plan

Y
female



- Protection level: IP67
- Temperature range: -30°C ... +60°C



4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

TPE violet, 2xAWG24	21348889487XXX
Type of cable	Part no.

All rights reserved Department HCS - RO HARTING Customised Solutions D-32339 Espelkamp		Tech. Character. Created by STOCHECIC Stocheci Title M12 Cable Assembly B-cod st/st m/f Type TB		Free size tol. Inspected by COSTEA Costea Standardisation MUNTEANV Muntean Date 2018-12-14 Number 21348889487XXX		According to production drawing State Final Release Doc-Key / ECM-Nr. 100806804/UGD/009/A 500000144878 Rev. A Page 1/1	
---	--	--	--	--	--	---	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21348889487005](#) [21348889487020](#) [21348889487015](#) [21348889487075](#) [21348889487010](#) [21348889487100](#)
[21348889487050](#)