




Connector Location A

Connector Location B



4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=40
	39	XXX=39
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

- Protection level: IP67
- Temperature range: -30°C ... +60°C

PVC violet, 2xAWG22	21348900486XXX
Type of cable	Part no.

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by COSTEA Costea	Inspected by MUNTEANV Muntean	Standardisation MUNTEANV Muntean	Date 2018-12-18	State Final Release	
	Department HCS - RO	Title M12 Cable Assembly B-cod st/- f/-				Doc-Key / ECM-Nr. 100579386/UGD/009/B 500000145021	
HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 21348900486XXX			Rev. B	Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348900486050](#) [21348900486010](#) [21348900486015](#) [21348900486020](#) [21348900486005](#) [21348900486075](#)
[21348900486100](#)