


Connector Location A





Connector Location B



X
male

Loading Plan

Y
female



4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

TPE violet, 2xAWG24	21349091487XXX
Type of cable	Part no.

- Protection level: IP67
- Temperature range: -30°C ... +80°C

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by STOCHECIC Stocheci		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean	
Department HCS - RO		Date 2019-03-27		State Final Release		Doc-Key / ECM-Nr. 100580614/UGD/009/C 500000149491	
HARTING Customised Solutions		Title M12 Cable Assembly B-cod an/an m/f		Rev. C		Page 1/1	
D-32339 Espelkamp		Type TB		Number 21349091487XXX			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21349091487005](#) [21349091487050](#) [21349091487075](#) [21349091487015](#) [21349091487020](#) [21349091487010](#)
[21349091487100](#)