



Connector Location A



Connector Location B



X
male



Loading Plan



4.0 to 100	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

Part no.	213494004XXXXX
Type of cable	XX
PVC green, 4xAWG22/7	XX=05
PUR green, 4xAWG22/7	XX=77

- Protection level: IP65/67
- Temperature range: -30°C ... +70°C

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by STOCHECIC Stocheci		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean	
Department HCS - RO		Title M12 Cable Assembly D-cod an/- m/-		Date 2019-03-27		State Final Release	
HARTING Customised Solutions		Type TB		Number 213494004XXXXX		Doc-Key / ECM-Nr. 100588495/UGD/000/F 500000149491	
D-32339 Espelkamp						Rev. F	
						Page 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

<u>21349400405010</u>	<u>21349400405015</u>	<u>21349400405020</u>	<u>21349400405075</u>	<u>21349400477010</u>	<u>21349400477075</u>
<u>21349400405100</u>	<u>21349400477005</u>	<u>21349400477100</u>	<u>21349400405005</u>	<u>21349400477015</u>	<u>21349400477050</u>
<u>21349400405050</u>	<u>21349400477020</u>	<u>21349400477030</u>	<u>21349400477200</u>	<u>21349400405250</u>	