





1	2	3	4	5	6	7	8
---	---	---	---	---	---	---	---

7	8
---	---



Loading-Plan:


-
- Diagram of a color wheel with five segments labeled 1 through 5. Segment 1 is black, 2 is blue, 3 is green-yellow, 4 is brown, and 5 is white. The segments are arranged in a circle, with 'PE' written on the left and right sides of the green-yellow segment.



4.0 to 100	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	<u>XXX</u>

Part no.	213496975XXXXX
Type of cable	XX
PVC grey, 5x1.5mm ²	XX=97
PUR black, 5x1.5mm ²	XX=98



All Dimensions
in mm

	Tech. Character.
--	------------------

Free size tol.

According to production drawing
2016-09-05



All rights reserved

Department HCS - RO

Created by
MUNTEANV

Inspected by	POPESCU
--------------	---------

Standardisation
AVRAM

Date	2016-10-18
------	------------

State
Final Release

Title 7/8" Cable Assembly

Type TB

Number	213496975XXXXX
--------	----------------

Doc-Key / ECM-Nr.
00581036/UGD/009/B
00000110271

Rev. **B**Page
1/1

- Protection level: IP 65/67
- Temperature range: -25°C ... +80°C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21349697597010](#) [21349697597015](#) [21349697598006](#) [21349697598010](#) [21349697597003](#) [21349697597006](#)
[21349697597020](#) [21349697598020](#) [21349697598003](#) [21349697598015](#) [21349697598030](#) [21349697597030](#)