




4.0 mm

0.1 mm

a

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
0.1	XXX=001	
Step	a [m]	<u>XXX</u>

Part no.	2134C7004.XX.XXX
Type of cable	XX
PVC, green, 4xAWG22/7	XX=05
PUR, green, 2x2xAWG22/7	XX=77

		All rights reserved Department HCS - RO		Created by COSTEA		Inspected by STOCHECIC		Standardisation MUNTEANV		Date 2018-09-28		State Final Release			
HARTING Customised Solutions D-32339 Espelkamp				Title M8 Cable Assembly D-cod st/- m/-								Doc-Key / ECM-Nr. 100705789/UGD/000/B 500000140779			
				Type TB		Number 2134C7004XXXXX						Rev. B		Page 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[2134C700477005](#) [2134C700477010](#) [2134C700477015](#) [2134C700477020](#) [2134C700477075](#) [2134C700477100](#)
[2134C700405100](#) [2134C700405075](#) [2134C700405015](#) [2134C700405020](#) [2134C700405005](#) [2134C700405010](#)
[2134C700477050](#) [2134C700405050](#)