





Loading-Plan
(Data)

- Shield
- | | |
|---|--------------|
| 1 | White/green |
| 2 | Green |
| 3 | White/orange |
| 4 | Blue |
| 5 | White/blue |
| 6 | Orange |
| 7 | White/brown |
| 8 | Brown |


Loading-Plan
DC version

- | | | |
|----|--------------|----|
| 1 | black | 1 |
| 2 | blue | 2 |
| PE | green/yellow | PE |

-Protection level: IP67
-Temperature range: -20°C ...+70°C

Data Part
-Transmission properties in accordance
with ISO/IEC 11801:2002: Class D.

???????R??



7	Hybrid cable 4x2AWG26/7+3x2,5 mm²	DC	33 57 111 080 0001	80 m
6	Hybrid cable 4x2AWG26/7+3x2,5 mm²	DC	33 57 111 060 0002	60 m
5	Hybrid cable 4x2AWG26/7+3x2,5 mm²	DC	33 57 111 040 0001	40 m
4	Hybrid cable 4x2AWG26/7+3x2,5 mm²	DC	33 57 111 020 0001	20 m
3	Hybrid cable 4x2AWG26/7+3x2,5 mm²	DC	33 57 111 010 0001	10 m
2	Hybrid cable 4x2AWG26/7+3x2,5 mm²	DC	33 57 111 005 0001	5 m
1	Hybrid cable 4x2AWG26/7+3x2,5 mm²	DC	33 57 111 001 0001	1 m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

			All Dimensions in mm Original Size DIN A 3			Nicht tol. Maße/ Free size tol.			Ref. MB		
							Oberflguete/ Surface qual.			Mat.	
							Oberflschutz/ Coating				
				V=		cm ³	A=		mm ²		
					Dat.		Name		Maßstab/ Scale 2:1		
				Detail.	20.05.08		MS				
				Insp.	20.05.08		RA				
				Stand.							
DRS648A	03.12.09	MS						Hybrid cable assembly, 4x2AWG26/7+3x2,5 mm ² HAN3A, DC			
35035	10.11.08	MS		HARTING Electronics GmbH & Co. KG D-32339 Espelkamp							TB 33 57 111 xxx 0001
34553											
Mod.	Dat.	Name									
			Sub.								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33571110010001](#) [33571110050001](#) [33571110100001](#) [33571110200001](#)