







-Insertion loss must be tested 100%
-Return loss must be tested at least
by random samples



4	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 020 5002	20 (±0.20)m
3	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 010 5002	10 (±0.10)m
2	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 005 5002	5 (±0.05)m
1	Hybrid cable 2xFO + 3x2.5/3.5	33 57 111 001 5002	1 (±0.01)m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maße/				
				Dat.	Name	Maßstab/Scale /	Hybrid cable assembly, FO 2xG50/125 + POWER 3x2.5/3.5, 1xHAN3A, LC duplex MM, 3xpower DC			
			Detail.	06.02.09	MR					
			Insp.							
			Stand.							
			HARTING Electronics GmbH & Co. KG				TB 33 57 111 xxx 5002			Blatt/ page
S468A			D-32339 ESPELKAMP							
Mod.	Dat.	Name				Sub.	Sub			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33571110015002](#) [33571110055002](#) [33571110105002](#) [33571110205002](#)