








-Insertion loss must be tested 100%
-Return loss must be tested at least
by random samples



4	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 020 5001	20 (± 0.20)m
3	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 010 5001	10 (± 0.10)m
2	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 005 5001	5 (± 0.05)m
1	Hybrid cable 2xFO+3x2.5/3.5	33 57 211 001 5001	1 (± 0.01)m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

			All Dimensions in mm Original Size DIN A 3				Techn. Character.			Nicht tolerierte Maße/		
									Maßstab/Scale /	Hybrid cable assembly, FO 2xG50/125 + POWER 3x2.5/3.5, 2xHAN3A, LC duplex MM, 3xpower AC		
			Detail.	06.02.09	MR							
			Insp.									
			Stand.									
										TB 33 57 211 xxx 5001		
S468A			HARTING Electronics GmbH & Co. KG									
Mod.	Dat.	Name	D-32339 ESPELKAMP						Sub.	Sub		Blatt/ page

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[33572110015001](#) [33572110055001](#) [33572110105001](#) [33572110205001](#)