

## Han 1A-3+PE-c-m shielded, latch



Image is for illustration purposes only. Please refer to product description.

Part number	09 10 003 3000
Specification	Han 1A-3+PE-c-m shielded, latch
HARTING eCatalogue	<a href="https://b2b.harting.com/09100033000">https://b2b.harting.com/09100033000</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> 1A

### Version

Termination method	Crimp termination
Gender	Male
Locking type	Snap-in latches
Size	1 A
Shielding	With cable tie
Number of contacts	3
Additional contacts	+ shielding
PE contact	Yes
Details	Please order crimp contacts separately. Order separately the hoods/housings for an IP65 performance.

A Han<sup>®</sup> 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector acc. to IEC 61984. In this case protection against electric shock must be provided by the installation methods of the user.

The Han<sup>®</sup> 1A insert has no conductive connection between PE-contact and shielding element. Protection against electric shock must be provided by connecting the cable shielding to a protective earth (PE).

Pack contents	Shielding element is included within the delivery
---------------	---

### Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm <sup>2</sup>
Rated current	10 A



Pushing Performance

## Technical characteristics

Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	$>10^8 \Omega$
Limiting temperature	-30 ... +90 °C
Mating cycles	$\geq 100$
Degree of protection acc. to IEC 60529	IP20

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
	IEC 61373 Category 1 Class B
	EN 60664-1
	IEC 61984
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	13.6 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09100033000