

## Han D-Sub module, crimp male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 009 3001
Specification	Han D-Sub module, crimp male
HARTING eCatalogue	<a href="https://b2b.harting.com/09140093001">https://b2b.harting.com/09140093001</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® D-Sub module

### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	9
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.08 ... 0.52 mm²
Rated current	5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

## Material properties

Material (insert)	Polycarbonate (PC) Zinc die-cast
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

## Commercial data

Packaging size	1
Net weight	32 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09140093001